

# Vise Accessories

Thanks to ongoing customer input, we've added important accessories to our product line and have made replacement parts available. If you have an idea or suggestion for an accessory or replacement part not shown here, please contact a PanaVise representative.

## Interchangeable Jaws Models 343, 344, 352-354

**Interchangeable Jaws for the 303 Standard and 304 Low-Profile Heads create the perfect Vise for the job!**



Model 343

Model 344



Model 352

Model 353



Model 354

### Nylon Jaws Model 343

- > Type 6/6 Nylon Jaws offer excellent electrical insulation and gentle holding power
- > Continuous heat tolerance to 200°F (93°C), intermittent heat to 300°F (149°C)

### Grooved Nylon Jaws Model 344

- > Same heat properties as 343 Nylon Jaws but with thin horizontal grooves, perfect for holding small tubes, rods, or small circuit boards firmly in place

### Teflon® High Heat Jaws Model 352

- > Recommended for high heat applications; won't scratch or mar delicate pieces
- > Continuous heat tolerance to 500°F (260°C)

### Plated Steel Jaws Model 353


- > Designed for firmly holding heavier objects in a high heat environment

### Brass Jaws Model 354

- > Non-marring alternative for heavy or high heat applications

## Neoprene Jaw Pads Models 204 & 346

**Neoprene Pads are soft but have plenty of holding power!**



Model 204

Model 346

### Neoprene Jaw Pads Model 204

#### For Models 201, 209 & 203 PV Jr. Head

- > Firmly hold your projects while protecting finished surfaces

### Neoprene Jaw Pads Model 346

#### For Models 366 & 376 Heads

- > Thick, molded pads have a corrugated surface on one side to firmly hold the most delicate objects
- > Reverse the pads and use the wide "V" groove to hold round objects
- > Jaw Pads are 1.875" (47.63mm) wide x 1.5" (38.1mm) tall