

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [19160-0041](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** Twist Lock Splice for 14-22 AWG Wire

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-19902-013 \(PDF\)](#)

**Agency Certification**

CSA LR700095  
 UL E32244

**General**

Product Family Splices  
 Series [19160](#)  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 MolexKits Yes  
 Overview [Splices](#)  
 Product Name Closed-End Twist Lock  
 UPC 800753110458

**Physical**

Barrel Type Closed  
 Color - Resin Orange  
 Flammability 94V-2  
 Insulation Nylon (PA)  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 1.341/g  
 Packaging Type Bag  
 Temperature Range - Operating 105°C  
 Wire Insulation Diameter 9.91mm max.  
 Wire Size AWG 14, 16, 18, 20, 22  
 Wire Size mm<sup>2</sup> 0.35 - 2.00

**Electrical**


Voltage - Maximum 600V

**Material Info**

Old Part Number TL-O

**Reference - Drawing Numbers**

Product Specification PS-19902-013  
 Sales Drawing SD-19160-005



**EU RoHS**

**ELV and RoHS  
 Compliant**  
**REACH SVHC**  
 Not Reviewed  
**Low-Halogen Status**  
 Not Reviewed

**China RoHS**



**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**  
 19160Series