

AC1200 Wireless Dual Band USB Adapter Archer T4U

⦿ Features:

- Dual-Band (IEEE 802.11b/g/n 2.4GHz, IEEE 802.11a/n/ac 5 GHz)
- Ultra-fast 1200 (867+300) Mbps wireless speed with 802.11ac
- Super Speed USB 3.0 port—Up to 10x faster than USB 2.0
- Easy wireless security encryption at a push of the WPS button
- WPA/WPA2 encryptions provide your network with active defense against security threats
- Bundled utility enables easy management
- Equipped with an USB Extension Cable for flexible deployment



⦿ Description:

TP-LINK's Archer T4U is an AC1200 Wireless Dual Band USB Adapter comes with the next generation Wi-Fi standard – 802.11ac, 3 times speeds of wireless N speeds, giving users the ability to access crystal clear 5GHz band at 867Mbps or legacy 2.4GHz connections at 300Mbps. Ultra-fast USB 3.0 perfectly match up with 802.11ac, and bundled extension cable—suitable for home deployment. With high-speed USB 3.0, Archer T4U breaks through the low-speed USB 2.0 limitation for 802.11ac high-speed experience, the Archer T4U is the superior choice for seamless HD streaming, online gaming and other bandwidth-intensive tasks.

⦿ Specifications:

HARDWARE FEATURES	
Interface	USB 3.0
Button	WPS Button
Dimensions (W X D X H)	3.6x1.2x0.6 in. (92.2x29x14.6mm)
Antenna Type	Omni Directional
Wireless Standards	IEEE 802.11a, IEEE 802.11ac, IEEE 802.11b, IEEE 802.11g, IEEE 802.11n

Frequency	5GHz 2.4GHz
Signal Rate	5GHz 11ac: Up to 867Mbps(dynamic) 11a: Up to 54Mbps(dynamic) 2.4GHz 11n: Up to 300Mbps(dynamic) 11g: Up to 54Mbps(dynamic) 11b: Up to 11Mbps(dynamic)
EIRP	<20dBm (EIRP)
Reception Sensitivity	5GHz: 11a 6Mbps: -88dBm 11a 54Mbps: -71dBm 11ac HT20: -65dBm 11ac HT40: -60dBm 11ac HT80: -56dBm 2.4GHz: 11b 11Mbps: -90dBm 11g 54Mbps: -73dBm 11n HT20: -71dBm 11n HT40: -68dBm
Wireless Modes	Ad-Hoc / Infrastructure mode
Wireless Security	Support 64/128 bit WEP, WPA-PSK/WPA2-PSK,802.1x
Modulation Technology	DBPSK, DQPSK, CCK, OFDM, 16-QAM, 64-QAM, 256-QAM
OTHERS	
Certification	CE, FCC, RoHS
Package Contents	Wireless Adapter Archer T4U Resource CD Quick Installation Guide USB Extension Cable
System Requirements	Windows 8/7/XP 32/64bits
Environment	Operating Temperature: 0°C~40°C (32°F~104°F) Storage Temperature: -40°C~70°C (-40°F~158°F) Operating Humidity: 10%~90% non-condensing Storage Humidity: 5%~90% non-condensing

Diagram:



Package:

- AC1200 Wireless Dual Band USB Adapter Archer T4U
- USB Extension Cable
- Quick Installation Guide
- Resource CD

Related Products:

- AC1350 Wireless Dual Band Gigabit Router Archer C5
- AC600 Wireless Dual Band USB Adapter Archer T2U