

Product Name : LED Holder Ø5, 2 pin Quadrate LED Holder
Item No. : LED-2




Features

- Stand LED lamp on circuit board
- Pad LED with distance from circuit board
- Suit for 5mm 2 pin LED lamp

Specification

MATERIAL: NYLON 66 (UL)
 FLAME CLASS: 94V-2
 COLOR: NATURAL
 *LED HOLDER WITH CONCAVE



FOR Ø5 2PIN LED				
PART NO	A	B	C	PACKAGE
LED-2	2.2	5.6	3.8	2000
LED-2.5	2.6	5.9	3.8	2000
LED-3	3.2	5.6	3.8	2000
*LED-3.6	3.6	5.6	3.8	2000
LED-4	4.1	5.6	3.8	2000
*LED-4.5	4.5	5.6	3.8	2000
*LED-5	5.0	5.6	3.8	2000
*LED-6	6.0	5.6	3.8	2000
*LED-6S	6.0	5.7	3.8	2000
*LED-6.8	6.8	5.6	3.8	2000

LED-7.5	7.5	5.6	3.8	2000
*LED-7.8	7.8	5.8	3.9	2000
*LED-8	8.0	5.6	3.8	2000
LED-8.8	8.8	5.6	3.8	2000
LED-9.8	9.8	5.6	3.8	2000
*LED-10A	10.0	5.9	3.9	2000
*LED-11A	11.0	5.8	3.8	1000
LED-12	12.0	5.8	3.9	1000
LED-15	15.0	5.6	3.9	1000
*LED-17	17.0	5.6	3.9	1000
LED-18.5	18.5	5.7	3.9	1000
*LED-2A	2.0	5.0	3.6	2000
*LED-2.5A	2.5	5.0	3.6	2000
*LED-3A	3.0	5.0	3.6	2000
*LED-3.5	3.5	5.0	3.6	2000
*LED-4C	4.0	5.0	3.6	2000
*LED-4.5A	4.5	5.0	3.6	2000
*LED-5A	5.0	5.0	3.6	2000
*LED-5.5	5.5	5.0	3.6	2000
*LED-6A	6.0	5.0	3.6	2000
*LED-6.5A	6.5	5.0	3.6	2000
*LED-7	7.0	5.0	3.6	2000
*LED-7.5A	7.5	5.0	3.6	2000
*LED-7.9	7.9	5.0	3.6	2000
*LED-8.5A	8.5	5.0	3.6	2000
*LED-9	9.0	5.0	3.6	2000
LED-9.5	9.5	5.0	3.5	2000
*LED-10	10.0	5.0	3.5	2000
*LED-10.6	10.7	5.1	3.6	1000
LED-11	11.0	5.0	3.8	1000
*LED-12A	12.0	5.0	3.2	1000
*LED-13	13.0	5.0	3.6	1000
*LED-13.8	13.8	5.0	3.7	1000
LED-14	14.0	5.0	3.7	1000
*LED-14A	14.0	5.0	3.7	1000
*LED-15A	15.2	5.0	3.7	1000
*LED-16	16.0	5.0	3.7	1000
*LED-16A	16.4	5.0	3.7	1000
*LED-18B	18.3	5.1	3.5	1000
*LED-19	19.0	5.0	3.9	1000
*LED-20	20.2	5.0	3.8	1000
LED-21	21.0	5.1	3.8	1000
*LED-22	22.0	5.1	3.9	1000
*LED-23	23.0	5.1	3.8	500
LED-24	24.0	5.8	3.9	500
LED-37	37.5	5.8	3.9	500