

Tenma 72-10200 Moisture Meters

Specifications	
Measuring principle:	Electrical resistance
Electrode length:	8mm
Electrodes:	Integrated, replaceable
Measuring range:	Wood: 6 - 44%
	Material: 0.2 – 2.0%
Display accuracy:	Wood: $\pm 1\%$
	Material: $\pm 0.05\%$
Auto power OFF:	After approx. 15 minutes
Battery:	3 x Cr2032, replaceable
Housing material:	Impact-proof plastic housing
Ambient temperature:	0 - 40°C
Ambient Relative humidity:	0 – 85 %RH
Dimensions:	139x47x25mm
Weight:	approximately 100g

