

Tenma 72-10204 Digital Tachometers

Specifications	
Display	5 digits LCD display
Accuracy	$\pm(0.05\%+1 \text{ digits})$
RPM test rang	2 to 99,999RPM
Count tang	1 to 99,999 REV
Resolution	0.1RPM (2 to 999.9RPM)
	1 RPM (over 1000 RPM)
Sampling time	0.5 sec. (over 120 RPM)
Detecting distance	50mm to 500mm
Time base	Quartz crystal
Power consumption	Approx 45mA
Power Supply	9V Battery or 6V Exterior DC
Operation temp	0°C to 50°C
Dimension	160x58x39mm
Weight	151g

