



Tenma 72-10450

## SPECIFICATIONS

Basic Functions	Range	Best Accuracy
Range	30-80dB	±1.5dB
	50-100dB	±1.5dB
	60-110dB	±1.5dB
	80-130dB	±1.5dB
Frequency	31.5Hz-8000Hz	✓
Frequency Weighting	A&C	✓
Sample Rate	FAST:8 Times/s	✓
	SLOW:1 Times/s	✓
<b>Special Functions</b>		
Analogue Outputs	Ω	✓
	:100Ω	✓
Data Hold		✓
Auto Power Off		✓
Low Battery Indication	≅ 4.8V	✓
MAX Mode		✓
MIN Mode		✓
Data Logging		63
High Alarm	Display "OVER"	✓
Lower Alarm	Display "UNDER"	✓
LCD Backlight		✓
Analogue Bar Graph	30-130dB	✓
<b>GENERAL CHARACTERISTICS</b>		
Power	1.5V Battery (LR6) x 4	
LCD Size	53 x 41mm	
Product Colour	Orange and Grey	
Product Net Weight	330g	
Product Size	273 x 70 x 39mm	
Standard Accessories	Batteries, Windscreen, Leather Cas	
Standard Individual Packing	Gift Box , English Manual	
Standard Quantity Per Carton	30pcs	
Standard Carton Measurement	670 x 385 x 300mm(0.077 CBM Per Standard Carton)	
Standard Carton Gross Weight	18kg	