

Model: 381 Vacuum Base PanaVise

The world's most PORTABLE work holding tool! Quickly attaches to any smooth, non-porous flat surface with the flip of a lever! Take it anywhere you need it for hobbies, electronics and small home repairs.

- Our Vacuum Base PanaVise is widely used for portable applications
- Single knob controls head movement through 3-planes: 90° Tilt, 360° Turn & 360° Rotation
- Jaws are 2.5" (63.5mm) wide, 0.5" (12.6mm) tall and open to 2.25" (57.1mm)
- Nylon jaws offer excellent electrical insulation and gentle holding power [continuous heat tolerance up to 200°F (93°C), intermittent heat to 300°F (149°C)]. Interchangeable jaws available
- Base accepts all 300 series Heads and any 5/8" (15.9mm) diameter shaft
- Pad footprint measures 5.125" x 4.25" (130.2mm x 108mm)
- Height: 6.125" (155.6mm), Weight: 2.8 lbs. (1.3kg)

