



PRODUCT SPECIFICATION

Brand	C.K
Product Range	Bolt Cutters
Catalogue number	4358, 4371
Date	18/02/2009

<p>Range Description Professional quality bolt cutters</p> <p>Features</p> <p>4358/4371</p> <ul style="list-style-type: none"> • For cutting round material and hard wire up to 40HRC • Heads and cutting edges manufactured from hot drop forged Chrome vanadium steel with induction hardened cutting edges for strength and durability 	 <p>4358</p>  <p>4371</p>
--	---

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T4358 12	Bolt Cutter 300mm	5013969553307	82034000	1
T4358 15	Bolt Cutter 380mm	5013969553406	82034000	1
T4358 18	Bolt Cutter 470mm	5013969553505	82034000	1
T4358 25	Bolt Cutter 630mm	5013969553604	82034000	1
T4358 30	Bolt Cutter 780mm	5013969553703	82034000	1
T4358 36	Bolt Cutter 900mm	5013969982701	82034000	1
T4371A	Bolt Cutter 250mm	5013969334005	82034000	2

Technical product information	Cutting capacities		
	Size mm	Cutting Capacity (Dia mm)	
		785N/mm2 (51Tons/Sq")	1226N/mm2 (80 Tons/Sq")
	250	5	3
	340	6	5
	400	7	6
	450	10	7
	610	11	9
800	13	11	
900	15	13	
Standards compliance	None applicable		
User health and safety information	Users and bystanders are advised to wear protective gloves and eye protection when using these products		
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations		
Material safety data	None applicable		
Warranty	C.K Tools are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered		
Country of origin	Germany		

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T4358 12	115	25	340	775	-	-	-	-
T4358 15	115	25	390	845	-	-	-	-
T4358 18	120	30	465	1720	-	-	-	-
T4358 25	150	35	620	2420	-	-	-	-
T4358 30	190	45	790	4620	-	-	-	-
T4358 36	190	45	910	4980	-	-	-	-
T4371A	80	20	255	462	110	23	330	484

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T4358 12						
T4358 15						
T4358 18						
T4358 25						
T4358 30						
T4358 36						
T4371A	100	300	65	1035		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T4358 12					8	Bag		
T4358 15					10	Bag		
T4358 18					10	Bag		
T4358 25					12	Bag		
T4358 30					12	Bag		
T4358 36					12	Bag		
T4371A	24	Wallet					68	Box