

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [51021-0400](#)
Status: **Active**
Overview: [PicoBlade™ Connector System](#)
Description: 1.25mm Pitch PicoBlade™ Wire-to-Wire and Wire-to-Board Housing, Female, 4 Circuits

Documents:

3D Model	Product Specification PS-51021-023 (PDF)
Drawing (PDF)	Product Specification PS-51021-024 (PDF)
Product Specification PS-51021-001 (PDF)	Product Specification PS-51021-025 (PDF)
Product Specification PS-51021-002 (PDF)	Product Specification PS-51021-026 (PDF)
Product Specification PS-51021-009 (PDF)	Product Specification PS-51021-027 (PDF)
Product Specification PS-51021-010 (PDF)	Product Specification PS-51021-028 (PDF)
Product Specification PS-51021-011 (PDF)	Packaging Specification SPK-51021-001 (PDF)
Product Specification PS-51021-022 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	51021
Application	Signal, Wire-to-Board, Wire-to-Wire
MolexKits	Yes
Overview	PicoBlade™ Connector System
Product Name	PicoBlade™
UPC	800753575615


Physical

Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	42.200/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Stackable	No
Temperature Range - Operating	-40°C to +85°C

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-51021-001
Product Specification	PS-51021-001, PS-51021-002, PS-51021-009, PS-51021-010, PS-51021-011, PS-51021-022, PS-51021-023, PS-51021-024, PS-51021-025, PS-51021-026, PS-51021-027, PS-51021-028, RPS-51021-001, RPS-51021-002, RPS-51021-003, RPS-51021-004, RPS-51021-006, RPS-51021-007, RPS-51021-008, RPS-51021-009, RPS-51021-010, RPS-51021-011, RPS-51021-013, RPS-51021-014,



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[51021Series](#)

Mates With

[53261](#) 1.25mm Pitch PicoBlade™ Header

Use With

[50058](#) Crimp Terminal, [50079](#) Crimp Terminal

RPS-51021-016, RPS-51021-018, RPS-51021-020,
RPS-51021-021, RPS-51021-022, RPS-51021-023,
RPS-51021-024, RPS-51021-025, RPS-51021-027,
RPS-51021-028, RPS-51021-030, RPS-51021-031,
RPS-51021-032, RPS-51021-033, RPS-51021-034,
RPS-51021-037, RPS-51021-038, RPS-51021-039,
RPS-51021-040, RPS-51021-041, RPS-51021-042,
RPS-51021-043, RPS-51021-044, RPS-51021-045,
RPS-51021-046, RPS-51021-047, RPS-51021-048,
RPS-51021-051, RPS-51021-052, RPS-51021-053,
RPS-51021-054, RPS-51021-055, RPS-51021-056,
RPS-51021-057, RPS-51021-058, RPS-51021-059,
RPS-51021-060, RPS-51021-061, RPS-51021-062,
RPS-51021-063, RPS-51021-064, RPS-51021-065,
RPS-51021-066, RPS-51021-067, RPS-51021-068,
RPS-51021-071, RPS-51021-072, RPS-51021-073,
RPS-51021-074, RPS-51021-076, RPS-51021-077,
RPS-51021-078, RPS-51021-079, RPS-51021-080,
RPS-51021-081, RPS-51021-084, RPS-51021-085,
RPS-51021-086, RPS-51021-089, RPS-51021-091,
RPS-51021-092, RPS-51021-096, RPS-51021-097,
RPS-51021-101, RPS-51021-102, RPS-51021-103,
RPS-51021-104, RPS-51021-105, RPS-51021-107,
RPS-51021-108, RPS-51021-110, RPS-51021-112,
RPS-51021-114, RPS-51021-117, RPS-51021-121,
RPS-51021-122, RPS-53398-002, RPS-53398-037,
RPS-53398-038
SD-51021-002, SD-51021-005

Sales Drawing

This document was generated on 04/15/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION