

6.02100.55

BS 14.4 LT Compact

14.4 Volt Cordless drill/screwdriver BS 14.4 LT Compact



0210055S_51.EPS

- Extremely powerful thanks to powerful Metabo 4-pole motor for quick drilling and screwdriving
- Spindle with hexagonal recess for screwdriver bits for working without chuck
- Integrated working light to illuminate the work site
- With handy belt hook and bit holder, can be fixed either on the right or left side
- Battery packs with capacity display for checking the charge status
- Ultra-M technology for highest performance, gentle charging, optimum energy utilisation and long service life.
- 3-year battery pack warranty by means of Ultra-M technology

Comparative technical values

Type of battery pack	Li-ion
Battery pack voltage	14,4 V
Capacity of battery pack	1,5 Ah
Maximum torque, soft	27 Nm
Maximum torque, hard	50 Nm
Adjustable torque	0,7 - 8 Nm
- Drill diameter in	
- Steel	13 mm
- Wood	35 mm
Idle revolutions	0 - 400 / 0 - 1.450 /min
Drill spindle thread	1/2 " - 20 UNF
Chuck adapter	1,5 - 13 mm
Weight (including battery pack)	1,5 kg

Scope of delivery

Quick-action Keyless Chuck, Belt hook with bit case, 2 Li-power battery packs (14.4 V/1.5 Ah), Charger ASC 30-36 V "AIR COOLED", Plastic Carry Case