

6.02191.89

BS 18 LTX Impuls

18 Volt Cordless drill/Screwdriver BS 18 LTX Impuls



0219189S_51.EPS

- Selectable "impuls" mode for removal of jammed screws and spot-drilling on smooth surfaces
- Extremely powerful thanks to powerful Metabo 4-pole motor for quick drilling and screwdriving
- Overload protection: protects the motor from overheating
- Spindle with hexagonal recess for screwdriver bits for working without chuck
- Neck (Ø 43 mm) for versatile use
- Integrated working light to illuminate the work site
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- With handy belt hook, can be fixed either on the right or left side
- Battery packs with capacity display for checking the charge status
- Ultra-M technology for highest performance, gentle charging, optimum energy utilisation and long service life.
- 3-year battery pack warranty by means of Ultra-M technology

Scope of delivery

Futuro Plus quick-action keyless chuck with metal sleeve, Side handle, Belt hooks, MetaLoc Case Insert, (without battery, without charger)

Comparative technical values

Battery pack voltage	18 V
Maximum torque, soft	55 Nm
Pulse torque	60 Nm
Maximum torque, hard	110 Nm
Adjustable torque	1,5 - 25 Nm
- Drill diameter in	
- Steel	13 mm
- Wood	65 mm
Idle revolutions	0 - 500 / 0 - 1.700 /min
Drill spindle thread	1/2 " - 20 UNF
Chuck adapter	1,5 - 13 mm
Weight (including battery pack)	2 kg