


Slide - Blue



Assembled
in the UK

4
GB

8
GB

16
GB

32
GB

INTRODUCTION

Transfer data without fuss with the Integral Slide. The USB has a capless design with a smooth thumb slide and is available in three eye-catching colours.

FEATURES

- Stylish slider USB
- Capless design with a smooth thumb slide
- Available in three eye-catching colours
- Quality durable casing, assembled in the UK

PRODUCT TYPE

USB Flash Drive

INTERFACE TYPE

Hi-Speed USB

INTERFACE CONNECTIVITY

1x Hi-Speed USB - 4 Pin USB Type A

COMPATIBILITY

Windows, XP, Vista, 7 and 8.
Mac OS 09 and Later.
Linux v2.4.0 and above.

ENVIRONMENTAL PARAMETERS

Min Operating Temperature 0°C
Max Operating Temperature 70°C

COMPLIANT STANDARD

Plug and Play

	LENGTH	WIDTH	DEPTH	WEIGHT
PRODUCT	54mm	21mm	10mm	10g
PACKED	170mm	105 mm	12mm	21g

CAPACITY	PART CODE	BARCODE (EAN)
4GB	INFD4GBSLDBL	5055288412644
8GB	INFD8GBSLDBL	5055288412705
16GB	INFD16GBSLDBL	5055288412675
32GB	INFD32GBSLDBL	5055288416710

This device should not be used as your sole backup.
Product design and specification subject to change or modification
without notice. E&OE. All trademarks acknowledged.
2 year warranty