

Black Box Products

Cables > Copper Patch Cables



CAT5 Solid-Conductor Patch Cable, PVC, Straight-Pinned, Beige, Custom Lengths



The ideal cable for 100-Mbps horizontal runs.

EYN737MS

Extended Double Diamond™ Warranty Available
(Lifetime)

Product Highlights

- This cable is ideal for backbone and horizontal runs.
- Solid conductor.
- Guaranteed for life!

Details

Description

CAT5 Solid-Conductor Patch Cable, PVC, Straight-Pinned, Beige, Custom Lengths

Quick Facts

- This cable is ideal for backbone and horizontal runs.
- Solid conductor.
- Guaranteed for life!

Further Details

- Supports ATM and 100BASE-TX up to 100 Mbps.
- Improves near-end crosstalk (NEXT).
- Better capacitance (15 pF/ft.) means less signal attenuation.
- Lower attenuation ratings at higher frequencies provide a better signal level.

Tech Spec

Technical Specifications for CAT5 Solid-Conductor Patch Cable, PVC, Straight-Pinned, Beige, Custom Lengths:

Cable Type	4-pair solid UTP
Conductor Gauge	24 AWG
Frequency	Up to 100 MHz
Impedance	100 \pm 15 ohms
Standards	TIA/EIA 568-B Category 5
Connectors	RJ-45

NOTE: Also available in blue. For details, contact our FREE Tech Support.
Technical specification weight is the unit weight. It is not the packaged shipping weight.