

## Black Box Products

---

### Cables > Modular/Telephone Cables



### RJ-11 Modular Cable, 6-Wire, Crossed-Pinning, 7-ft. (2.1-m)

Flat satin 4- or 6-wire cabling for voice and data.

EL06M-07

---

Extended Double Diamond™ Warranty Available  
(Lifetime)

#### Product Highlights

- Stranded conductor.
- High-quality flat-satin cable for data and voice applications.
- All-purpose cable is for voice and data applications running up to 1 Mbps.
- Not recommended for Token Ring or Ethernet applications.
- Guaranteed for life!

## Details

### Description

RJ-11 Modular Cable, 6-Wire, Crossed-Pinning, 7-ft. (2.1-m)

### Quick Facts

- Stranded conductor.
- High-quality flat-satin cable for data and voice applications.
- All-purpose cable is for voice and data applications running up to 1 Mbps.
- Not recommended for Token Ring or Ethernet applications.
- Guaranteed for life!

## Tech Spec

### Technical Specifications for RJ-11 Modular Cable, 6-Wire, Crossed-Pinning, 7-ft. (2.1-m):

<b>Cable Construction</b>	Gray flat satin, PVC
<b>Conductor Gauge</b>	28 AWG
<b>Distance (Maximum)</b>	As per equipment specifications
<b>Mutual Capacitance</b>	22 pF/ft.
<b>Resistance</b>	45 ohms/1000 ft.
<b>Connectors</b>	EL04MS, EL04M: 4-wire; EL06MS, EL06M: 6-wire

NOTE: For pinning info, click on "Application Diagrams."

Technical specification weight is the unit weight. It is not the packaged shipping weight.