

Steel Rules


SERIES 182

FEATURES

- Clear graduations on satin-chrome finish.
- Stainless tempered.



182-125



182-110

SPECIFICATIONS

Wide Rigid Rules (thickness 3/64")

Order No.	Black Chrome Rule Order No.	Size	Graduations				Width	Accuracy (Length)
182-101	182-109	6"(4R)	1/8	1/16	1/32	1/64th	3/4"	+0.004" / -0.0035" (+0.1mm / -0.09mm)
182-102	182-112	6"(16R)	1/32	1/64	1/50	1/100th	3/4"	
182-103	182-110	6"(5R)	1/32	1/64	1/10	1/100th	3/4"	
182-104	182-113	6"(3R)	1/32	1/64	1/10	1/50th	3/4"	
182-105	182-114	6" x 150mm	1/32	1/64	1mm	0.5mm	3/4"	
182-106	—	6" x 150mm	1/50	1/100	1mm	0.5mm	3/4"	
182-107	—	6" x 150mm	1/10	1/100	1mm	0.5mm	3/4"	
182-108	—	6" x 150mm	1/10	1/50	1mm	0.5mm	3/4"	
182-111	182-115	150mm	1mm	0.5mm	1mm	0.5mm	19mm	
182-112	182-127	12"(4R)	1/8	1/16	1/32	1/64th	1"	
182-122	182-129	12"(16R)	1/32	1/64	1/50	1/100th	1"	
182-123	182-128	12"(5R)	1/32	1/64	1/10	1/100th	1"	
182-124	—	12"(3R)	1/32	1/64	1/10	1/50th	1"	
182-125	182-130	12" x 300mm	1/32	1/64	1mm	0.5mm	1"	
182-126	—	12" x 300mm	1/50	1/100	1mm	0.5mm	1"	
182-131	182-132	300mm	1mm	0.5mm	1mm	0.5mm	25mm	+0.006" / -0.0035" (+0.15mm / -0.09mm)
182-241	182-146	18"(4R)	1/8	1/16	1/32	1/64	13/16"	
182-142	182-148	18"(16R)	1/32	1/64	1/50	1/100th	13/16"	
182-143	182-147	18"(5R)	1/32	1/64	1/10	1/100th	13/16"	
182-144	—	18"(3R)	1/32	1/64	1/10	1/50th	13/16"	
182-145	—	18" x 450mm	1/32	1/64	1mm	0.5mm	13/16"	
182-151	—	450mm	1mm	0.5mm	1mm	0.5mm	30mm	+0.007" / -0.0035" (+0.18mm / -0.09mm)
182-161	182-166	24"(4R)	1/8	1/16	1/32	1/64	13/16"	
182-162	182-168	24"(16R)	1/32	1/64	1/50	1/100th	13/16"	
182-163	182-167	24"(5R)	1/32	1/64	1/10	1/100th	13/16"	
182-164	—	24"(3R)	1/32	1/64	1/10	1/50th	13/16"	
182-165	—	24" x 600mm	1/32	1/64	1mm	0.5mm	13/16"	
182-171	—	600mm	1mm	0.5mm	1mm	0.5mm	30mm	+0.008" / -0.004" (+0.2mm / -0.1mm)
182-401	—	36"(4R)	1/8	1/16	1/32	1/64	1 1/4"	
182-403	—	36"(16R)	1/32	1/64	1/50	1/100th	1 1/4"	
182-405	—	36"(5R)	1/32	1/64	1/10	1/100th	1 1/4"	
182-406	—	36" x 900mm	1/32	1/64	1mm	0.5mm	1 1/4"	
182-402	—	48"(4R)	1/8	1/16	1/32	1/64	1 1/4"	
182-404	—	48"(16R)	1/32	1/64	1/50	1/100th	1 1/4"	
182-407	—	48" x 1219.2mm	1/32	1/64	1mm	0.5mm	1 1/4"	