

# Semi-Flexible Rules

## SERIES 182

### FEATURES

- Engraved on frontside only



182-304

### SPECIFICATIONS

Inch/Metric								
Order No.	Size	Graduations					Width	Accuracy (Length)
182-301	4" x 100mm	1/2mm	1mm	1/32	1/64	1/16th	5/8"	+0.004" / -0.0035"
182-302	6" x 150mm	1/2mm	1mm	1/32	1/64	1/16th	5/8"	(+0.1mm / -0.09mm)
182-303	8" x 200mm	1/2mm	1mm	1/32	1/64	1/16th	5/8"	
182-304	10" x 250mm	1/2mm	1mm	1/32	1/64	1/16th	5/8"	+0.005" / -0.0035"
182-305	12" x 300mm	1/2mm	1mm	1/32	1/64	1/16th	5/8"	+0.13mm / -0.09mm)
182-307	20" x 500mm	1/2mm	1mm	1/32	1/64	1/16th	5/8"	+0.007" / -0.0035" (+0.18mm / -0.09mm)
182-309	40" x 1000mm	1/2mm	1mm	1/32	1/64	1/16th	5/8"	+0.008" / -0.004" (+0.2mm / -0.1mm)

# Hook Rules

## SERIES 182

### FEATURES

- Hardened and tempered tool steel.
- Hard chrome finish.
- Furnished with adjustable hook.



182-421

### SPECIFICATIONS

Order No.	Size	Graduations					Width	Accuracy (Length)
182-421	6" (4R)	1/8	1/16	1/32	1/64	3/4"	+0.004" / -0.0035"	
182-422	12" (4R)	1/8	1/16	1/32	1/64	1"	+0.005" / -0.0035"	
182-423	18" (4R)	1/8	1/16	1/32	1/64	1-1/8"	+0.006" / -0.0035"	
182-424	24" (4R)	1/8	1/16	1/32	1/64	1-1/8"	+0.007" / -0.0035"	

# Pocket Steel Rule

## SERIES 950

### FEATURES

- Engraved on frontside only.
- Backside: Inch/Metric equivalents



950-300

### SPECIFICATIONS

Order No.	Size	Graduation		Width	Accuracy (Length)
950-300	6" x 150mm	1mm	1/64ths	1/2"	+0.004" / -0.0035" (+0.1mm / -0.09mm)
950-301	6"	1/32mths	1/64ths	1/2"	+0.004" / -0.0035"