

Product 15172

Number:



Order 65BR30/FL/CVP 130V

Abbreviation:

General Incandescent BR30 Reflector Lamp Inside Frost Finish Medium Aluminum

Description: Base 65Watt 130Volt Flood Beam Commercial Value Pack 6Bulbs Per Case
6Bulbs Per Package

*** Full Case Required**

Product Information

Abbrev. With Packaging Info.	65BR30FLCVP 130V 6/CS 6/SKU
Approx. Lumens	540
Average Rated Life (hr)	2000
Base	Medium
Beam Angle (deg)	60
Beam Type	FL
Bulb	BR30
Centerbeam Candlepower (cp)	370
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	3.752
Diameter (mm)	95.30
Filament	CC-6
Lamp Finish	Reflector
Maximum Overall Length - MOL (in)	5.375
Maximum Overall Length - MOL (mm)	136.525
Nominal Voltage (V)	130.00
Nominal Wattage (W)	65.00



Footnotes

- Should not be used in equipment where base temperature will exceed 500F.
- Operate only in porcelain sockets.
- Should be shielded against moisture falling on bulb.
- May not give satisfactory performance if any accessory lighting equipment touches the glass bulb.