

TLS 2200® General ID Materials

www.BradyID.com/tls2200

TLS 2200® General Identification Materials:

B-424 Paper Material

Color: White **Finish: Matte**

White paper material with matte finish and smooth top coat finish for thermal transfer printing. Good contrast and smear resistance for thermal barcode printing. Used for general purpose labeling applications.

Performance Attributes: 




Figure 29




Figure 40



| Diagram | Part Number | B-# | Material | Color | Label Width A Inch (mm) | Label Height B Inch (mm) | Labels Per Row | Labels Per Pkg | Rec. Ribbon |
|---------|--------------|-------|----------|-------|-------------------------|--------------------------|----------------|----------------|-------------|
| Fig. 29 | PTL-80-424 | B-424 | Paper | White | 0.750 (19.1) | 0.900 (22.9) | 1 | 250 | R4310 |
| Fig. 29 | BPTL-20-424 | B-424 | Paper | White | 1.000 (25.4) | 2.000 (50.8) | 1 | 1000 | R4310 |
| Fig. 40 | PTPSL-17-424 | B-424 | Paper | White | 1.000 (25.4) | 0.500 (12.7) | 1 | 500 | R4310 |
| Fig. 29 | PTL-20-424 | B-424 | Paper | White | 2.000 (50.8) | 1.000 (25.4) | 1 | 100 | R4310 |
| Fig. 40 | PTPSL-20-424 | B-424 | Paper | White | 2.000 (50.8) | 1.000 (25.4) | 1 | 100 | R4310 |
| Fig. 29 | PTL-22-424 | B-424 | Paper | White | 3.000 (76.2) | 1.000 (25.4) | 1 | 100 | R4310 |
| Fig. 29 | PTL-37-424 | B-424 | Paper | White | 3.000 (76.2) | 1.900 (48.3) | 1 | 100 | R4310 |
| Fig. 29 | PTL-38-424 | B-424 | Paper | White | 4.000 (101.6) | 1.900 (48.3) | 1 | 100 | R4310 |

TLS 2200® General Identification Materials:



B-425 Polypropylene Material

Color: White **Finish: Matte**

White polypropylene material stock with matte/opaque finish for thermal transfer printing or write-on applications. Excellent solvent resistance and print performance; not recommended for long-term outdoor use.

Performance Attributes: 




Figure 29




Figure 47




Figure 48



| Diagram | Part Number | B-# | Material | Color | Label Width A Inch (mm) | Label Height B Inch (mm) | Labels Per Row | Labels Per Pkg | Rec. Ribbon |
|---------|--------------|-------|---------------|-------|-------------------------|--------------------------|----------------|----------------|-------------|
| Fig. 29 | PTL-10-425 | B-425 | Polypropylene | White | 0.750 (19.1) | 0.250 (6.4) | 1 | 750 | R6210 |
| Fig. 47 | PTLFP-01-425 | B-425 | Polypropylene | White | 1.180 (30.0) | 0.788 (20.0) | 1 | 250 | R6210 |
| Fig. 48 | PTLFT-01-425 | B-425 | Polypropylene | White | 1.180 (30.0) | 0.788 (20.0) | 1 | 250 | R6210 |
| Fig. 47 | PTLFP-02-425 | B-425 | Polypropylene | White | 1.750 (44.5) | 1.000 (25.4) | 1 | 100 | R6210 |



Did You Know? LabelMark™ Labeling Software

LabelMark™ 5 Standard Software offers a variety of new tools and features for data management, label design and label printing and are all available for use with the TLS 2200® and TLS PC Link™ printers.

- Quickly create, view, and print with easy editing features
- Edit, view, and import data for multiple labels at once
- Quick printing with Brady printers and label materials

For more information, visit www.BradyID.com/labelmark.



View the Material Brands & Attributes Guide on page 4.
 TLS2200® Printer Ribbons on page 67.
 Full Material Properties on page 187.