

PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	C.K
Product Range	Standard screwdriver bits
Catalogue number	As listed
Date	24/10/2008

Range Description

A range of professional quality Chrome Vanadium screwdriver bits

Features

- Chrome vanadium steel
- Precision machined
- Grip Tip anti cam out ribs which positively engage with the screw head to reduce the risk of slip and cam out (* marked items only)

featuring **GRIP TIP™**
technology
ON SELECTED SIZES



Item Number	Item Description	EAN No	Commodity code	Carton Qty
T4545 1	Modulo Terminal Bit Size1 Card/2	5013969988772	82054000	20
T4545 2	Modulo Terminal Bit Size2 Card/2	5013969988789	82054000	20
422001	Modulo Terminal Bit Size1&2 Card/2	5051074220011	82054000	6
T4550 0645	Screwdriver Bit Slotted 0.6x4.5mm Loose		82054000	10
T4550 0855	Screwdriver Bit Slotted 0.8x5.5mm Loose *		82054000	10
T4550 1055	Screwdriver Bit Slotted 1.0x5.5mm Loose *		82054000	10
T4550 1265	Screwdriver Bit Slotted 1.2x6.5mm Loose *		82054000	10
T4550-0645T	Screwdriver Bit Slotted 0.6x4.5mm Card/2 *	5013969702279	82054000	25
T4550-0855T	Screwdriver Bit Slotted 0.8x5.5mm Card/2 *	5013969702286	82054000	25
T4550-1055T	Screwdriver Bit Slotted 1.0x5.5mm Card/2 *	5013969702293	82054000	25
T4550-1265T	Screwdriver Bit Slotted 1.2x6.5mm Card/2 *	5013969702309	82054000	25
T4551 1	Screwdriver Bit PH1 Loose *		82054000	10
T4551 2	Screwdriver Bit PH2 Loose *		82054000	10
T4551 3	Screwdriver Bit PH3 Loose *		82054000	10
T4552 1	Screwdriver Bit PZD/SDV 1 Loose *		82054000	10
T4552 2	Screwdriver Bit PZD/SDV 2 Loose *		82054000	10
T4552 3	Screwdriver Bit PZD/SDV 3 Loose *		82054000	10
T4552 4	Screwdriver Bit PZD/SDV 4 Loose *		82054000	10
T4553 1	Screwdriver Bit Robertson 1 Loose		82054000	10
T4553 2	Screwdriver Bit Robertson 2 Loose		82054000	10
T4553 3	Screwdriver Bit Robertson 3 Loose		82054000	10
T4554 25	Screwdriver Bit Hex 2.5mm Loose		82054000	10
T4554 3	Screwdriver Bit Hex 3.0mm Loose		82054000	10
T4554 4	Screwdriver Bit Hex 4.0mm Loose		82054000	10
T4554 5	Screwdriver Bit Hex 5.0mm Loose		82054000	10
T4554 6	Screwdriver Bit Hex 6.0mm Loose		82054000	10
T4554-3T	Screwdriver Bit Hex 3.0mm Card/2	5013969702316	82054000	25
T4554-4T	Screwdriver Bit Hex 4.0mm Card/2	5013969702323	82054000	25
T4554-5T	Screwdriver Bit Hex 5.0mm Card/2	5013969702330	82054000	25
T4554-6T	Screwdriver Bit Hex 6.0mm Card/2	5013969702347	82054000	25
T4555 1	Screwdriver Bit PH1x50mm Loose *		82054000	10
T4555 2	Screwdriver Bit PH2x50mm Loose *		82054000	10
T4555-1T	Screwdriver Bit PH1x50mm Card/2 *	5013969702361	82054000	25
T4555-2T	Screwdriver Bit PH2x50mm Card/2 *	5013969702378	82054000	25
T4556 1	Screwdriver Bit PZD1x50mm Loose *		82054000	10
T4556 2	Screwdriver Bit PZD2x50mm Loose *		82054000	10
T4556-1T	Screwdriver Bit PZD1x50mm Card/2 *	5013969702385	82054000	25
T4556-2T	Screwdriver Bit PZD2x50mm Card/2 *	5013969702392	82054000	25

T4557 05	Screwdriver Bit 4557 TX05 Loose		82054000	10
T4557 06	Screwdriver Bit 4557 TX06 Loose		82054000	10
T4557 07	Screwdriver Bit 4557 TX07 Loose		82054000	10
T4557 08	Screwdriver Bit 4557 TX08 Loose		82054000	10
T4557 09	Screwdriver Bit 4557 TX09 Loose		82054000	10
T4557 10	Screwdriver Bit 4557 TX10 Loose		82054000	10
T4557 15	Screwdriver Bit 4557 TX15 Loose		82054000	10
T4557 20	Screwdriver Bit 4557 TX20 Loose		82054000	10
T4557 25	Screwdriver Bit 4557 TX25 Loose		82054000	10
T4557 27	Screwdriver Bit 4557 TX27 Loose		82054000	10
T4557 30	Screwdriver Bit 4557 TX30 Loose		82054000	10
T4557 40	Screwdriver Bit 4557 TX40 Loose		82054000	10
T4557-05T	Screwdriver Bit 4557 TX05 Card/2	5013969702408	82054000	25
T4557-06T	Screwdriver Bit 4557 TX06 Card/2	5013969702415	82054000	25
T4557-07T	Screwdriver Bit 4557 TX07 Card/2	5013969702422	82054000	25
T4557-08T	Screwdriver Bit 4557 TX08 Card/2	5013969702439	82054000	25
T4557-09T	Screwdriver Bit 4557 TX09 Card/2	5013969702446	82054000	25
T4557-10T	Screwdriver Bit 4557 TX10 Card/2	5013969702453	82054000	25
T4557-15T	Screwdriver Bit 4557 TX15 Card/2	5013969702460	82054000	25
T4557-20T	Screwdriver Bit 4557 TX20 Card/2	5013969702477	82054000	25
T4557-25T	Screwdriver Bit 4557 TX25 Card/2	5013969702484	82054000	25
T4557-27T	Screwdriver Bit 4557 TX27 Card/2	5013969702491	82054000	25
T4557-30T	Screwdriver Bit 4557 TX30 Card/2	5013969702507	82054000	25
T4557-40T	Screwdriver Bit 4557 TX40 Card/2	5013969702514	82054000	25
T4557T 10	Screwdriver Bit TX10 Tamperproof Loose		82054000	10
T4557T 15	Screwdriver Bit TX15 Tamperproof Loose		82054000	10
T4557T 20	Screwdriver Bit TX20 Tamperproof Loose		82054000	10
T4557T 25	Screwdriver Bit TX25 Tamperproof Loose		82054000	10
T4557T 30	Screwdriver Bit TX30 Tamperproof Loose		82054000	10
T4557T-10T	Screwdriver Bit TX10 Tamperproof Card/2	5013969702521	82054000	25
T4557T-15T	Screwdriver Bit TX15 Tamperproof Card/2	5013969702538	82054000	25
T4557T-20T	Screwdriver Bit TX20 Tamperproof Card/2	5013969702545	82054000	25
T4557T-25T	Screwdriver Bit TX25 Tamperproof Card/2	5013969702552	82054000	25
T4557T-30T	Screwdriver Bit TX30 Tamperproof Card/2	5013969702569	82054000	25
T4561 1	Screwdriver Bit PH 1 Card/2 *	5013969819700	82054000	25
T4561 2	Screwdriver Bit PH 2 Card/2 *	5013969819809	82054000	25
T4561 3	Screwdriver Bit PH 3 Card/2 *	5013969819908	82054000	25
T4562 1	Screwdriver Bit PZD 1 Card/2 *	5013969820003	82054000	25
T4562 2	Screwdriver Bit PZD 2 Card/2 *	5013969820102	82054000	25
T4562 3	Screwdriver Bit PZD 3 Card/2 *	5013969820201	82054000	25

T4562 4	Screwdriver Bit PZD 4 Card/2 *	5013969702729	82054000	25
T4562-215	Screwdriver Bit PZD2 Box /15 *	5013969702736	82054000	100
T4562-2CB	Screwdriver Bit PZD2 Counter Box of 12xT4562-215 *	5013969702743	82054000	18
T4579-1T	Screwdriver Bit PZD1xSlotted 4mm Card/2 *	5013969702774	82054000	25
T4579-2T	Screwdriver Bit PZD2xSlotted 7mm Card/2 *	5013969702781	82054000	25

Technical product information	
Standards compliance	All 25mm Bits have DIN 3126-C6,3. ISO 1173 drive All 50mm single ended bits have DIN 3126-E6,3. ISO 1173 drive
User health and safety information	
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K screwdriver bits are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	China Germany for T4545 1 & 2

Dimensional details

Item	Product only (Not on packaging)				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T4545 1	7	7	50	10	50	8	127	26
T4545 2	7	7	50	10	50	8	127	27
422001	7	7	50	10	75	15	125	34
T4550 0645	7	7	25	4	-	-	-	-
T4550 0855	7	7	25	4	-	-	-	-
T4550 1055	7	7	25	4	-	-	-	-
T4550 1265	7	7	25	4	-	-	-	-
T4550-0645T	7	7	25	4	50	8	127	13.2
T4550-0855T	7	7	25	4	50	8	127	14
T4550-1055T	7	7	25	4	50	8	127	14
T4550-1265T	7	7	25	4	50	8	127	14.4

T4551 1	7	7	25	4	-	-	-	-
T4551 2	7	7	25	4	-	-	-	-
T4551 3	7	7	25	4	-	-	-	-
T4552 1	7	7	25	4	-	-	-	-
T4552 2	7	7	25	4	-	-	-	-
T4552 3	7	7	25	4	-	-	-	-
T4552 4	7	7	25	4	-	-	-	-
T4553 1	7	7	25	4	-	-	-	-
T4553 2	7	7	25	4	-	-	-	-
T4553 3	7	7	25	4	-	-	-	-
T4554 25	7	7	25	4	-	-	-	-
T4554 3	7	7	25	4	-	-	-	-
T4554 4	7	7	25	4	-	-	-	-
T4554 5	7	7	25	4	-	-	-	-
T4554 6	7	7	25	4	-	-	-	-
T4554-3T	7	7	25	4	50	8	127	13.6
T4554-4T	7	7	25	4	50	8	127	14.2
T4554-5T	7	7	25	4	50	8	127	15.6
T4554-6T	7	7	25	4	50	8	127	17
T4555 1	7	7	50	10	-	-	-	-
T4555 2	7	7	50	10	-	-	-	-
T4555-1T	7	7	50	10	50	8	127	25.6
T4555-2T	7	7	50	10	50	8	127	26.4
T4556 1	7	7	50	10	-	-	-	-
T4556 2	7	7	50	10	-	-	-	-
T4556-1T	7	7	50	10	50	8	127	26
T4556-2T	7	7	50	10	50	8	127	26.6
T4557 05	7	7	25	3	-	-	-	-
T4557 06	7	7	25	3	-	-	-	-
T4557 07	7	7	25	3	-	-	-	-
T4557 08	7	7	25	3	-	-	-	-
T4557 09	7	7	25	3	-	-	-	-
T4557 10	7	7	25	4	-	-	-	-
T4557 15	7	7	25	4	-	-	-	-
T4557 20	7	7	25	4	-	-	-	-
T4557 25	7	7	25	4	-	-	-	-
T4557 27	7	7	25	4	-	-	-	-

T4557 30	7	7	25	4	-	-	-	-
T4557 40	7	7	25	4	-	-	-	-
T4557-05T	7	7	25	3	50	8	127	11.8
T4557-06T	7	7	25	3	50	8	127	12.2
T4557-07T	7	7	25	3	50	8	127	12.2
T4557-08T	7	7	25	3	50	8	127	12.8
T4557-09T	7	7	25	3	50	8	127	13
T4557-10T	7	7	25	4	50	8	127	13
T4557-15T	7	7	25	4	50	8	127	13.2
T4557-20T	7	7	25	4	50	8	127	13.6
T4557-25T	7	7	25	4	50	8	127	14
T4557-27T	7	7	25	4	50	8	127	14.4
T4557-30T	7	7	25	4	50	8	127	15
T4557-40T	7	7	25	4	50	8	127	16
T4557T 10	7	7	25	4	-	-	-	-
T4557T 15	7	7	25	4	-	-	-	-
T4557T 20	7	7	25	4	-	-	-	-
T4557T 25	7	7	25	4	-	-	-	-
T4557T 30	7	7	25	4	-	-	-	-
T4557T-10T	7	7	25	4	50	8	127	13
T4557T-15T	7	7	25	4	50	8	127	13
T4557T-20T	7	7	25	4	50	8	127	13.6
T4557T-25T	7	7	25	4	50	8	127	14
T4557T-30T	7	7	25	4	50	8	127	15
T4561 1	7	7	25	4	50	8	127	13
T4561 2	7	7	25	4	50	8	127	14
T4561 3	7	7	25	4	50	8	127	15
T4562 1	7	7	25	4	50	8	127	13.4
T4562 2	7	7	25	4	50	8	127	14.2
T4562 3	7	7	25	4	50	8	127	15
T4562 4	7	7	25	4	50	8	127	18.6
T4562-215	7	7	25	4	44	24	81	93
T4562-2CB	7	7	25	4	170	135	75	1220
T4579-1T	7	7	50	10	50	8	127	28.5
T4579-2T	7	7	50	10	50	8	127	30.6

Item	Shelf (Inner) box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T4545 1	80	200	50	540		
T4545 2	80	200	50	565		
422001	85	230	50	262		
T4550 0645	140	180	170	2250		
T4550 0855	140	180	170	2450		
T4550 1055	140	180	170	2450		
T4550 1265	140	180	170	2550		
T4550-0645T	60	210	143	380		
T4550-0855T	60	210	143	400		
T4550-1055T	60	210	143	400		
T4550-1265T	60	210	143	410		
T4551 1	140	180	170	2250		
T4551 2	140	180	170	2450		
T4551 3	140	180	170	2700		
T4552 1	140	180	170	2350		
T4552 2	140	180	170	2550		
T4552 3	140	180	170	2690		
T4552 4	140	180	170	3630		
T4553 1	140	180	170	2350		
T4553 2	140	180	170	2500		
T4553 3	140	180	170	2650		
T4554 25	140	180	170	2250		
T4554 3	140	180	170	2350		
T4554 4	140	180	170	2650		
T4554 5	140	180	170	2950		
T4554 6	140	180	170	3050		
T4554-3T	60	210	143	390		
T4554-4T	60	210	143	405		
T4554-5T	60	210	143	440		
T4554-6T	60	210	143	475		
T4555 1	140	180	170	5200		

T4555 2	140	180	170	5250		
T4555-1T	60	210	143	690		
T4555-2T	60	210	143	710		
T4556 1	140	180	170	5350		
T4556 2	140	180	170	5600		
T4556-1T	60	210	143	700		
T4556-2T	60	210	143	715		
T4557 05	140	180	170	1900		
T4557 06	140	180	170	2050		
T4557 07	140	180	170	2050		
T4557 08	140	180	170	2050		
T4557 09	140	180	170	2050		
T4557 10	140	180	170	2200		
T4557 15	140	180	170	2200		
T4557 20	140	180	170	2350		
T4557 25	140	180	170	2500		
T4557 27	140	180	170	2550		
T4557 30	140	180	170	2700		
T4557 40	140	180	170	2950		
T4557-05T	60	210	143	345		
T4557-06T	60	210	143	355		
T4557-07T	60	210	143	355		
T4557-08T	60	210	143	370		
T4557-09T	60	210	143	375		
T4557-10T	60	210	143	375		
T4557-15T	60	210	143	380		
T4557-20T	60	210	143	390		
T4557-25T	60	210	143	400		
T4557-27T	60	210	143	410		
T4557-30T	60	210	143	425		
T4557-40T	60	210	143	450		
T4557T 10	140	180	170	2200		
T4557T 15	140	180	170	2200		
T4557T 20	140	180	170	2400		
T4557T 25	140	180	170	2400		
T4557T 30	140	180	170	2550		
T4557T-10T	60	210	143	375		

T4557T-15T	60	210	143	375		
T4557T-20T	60	210	143	390		
T4557T-25T	60	210	143	400		
T4557T-30T	60	210	143	425		
T4561 1	60	210	143	375		
T4561 2	60	210	143	400		
T4561 3	60	210	143	425		
T4562 1	60	210	143	385		
T4562 2	60	210	143	405		
T4562 3	60	210	143	425		
T4562 4	60	210	143	515		
T4562-215	120	140	230	4700		
T4562-2CB	540	420	200	22900		
T4579-1T	60	210	143	762.5		
T4579-2T	60	210	143	815		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T4545 1	0.6	Blister	3	Card			65	Box
T4545 2	0.6	Blister	3	Card			65	Box
422001	2	Blister	4	Card			58	Box
T4550 0645	1	Bag					56	Box
T4550 0855	1	Bag					56	Box
T4550 1055	1	Bag					56	Box
T4550 1265	1	Bag					56	Box
T4550-0645T	0.6	Blister	4	Backing card			56	Box
T4550-0855T	0.6	Blister	4	Backing card			56	Box
T4550-1055T	0.6	Blister	4	Backing card			56	Box
T4550-1265T	0.6	Blister	4	Backing card			56	Box
T4551 1	1	Bag					56	Box
T4551 2	1	Bag					56	Box
T4551 3	1	Bag					56	Box
T4552 1	1	Bag					56	Box
T4552 2	1	Bag					56	Box

T4552 3	1	Bag					56	Box
T4552 4	1	Bag					56	Box
T4553 1	1	Bag					56	Box
T4553 2	1	Bag					56	Box
T4553 3	1	Bag					56	Box
T4554 25	1	Bag					56	Box
T4554 3	1	Bag					56	Box
T4554 4	1	Bag					56	Box
T4554 5	1	Bag					56	Box
T4554 6	1	Bag					56	Box
T4554-3T	0.6	Blister	4	Backing card			56	Box
T4554-4T	0.6	Blister	4	Backing card			56	Box
T4554-5T	0.6	Blister	4	Backing card			56	Box
T4554-6T	0.6	Blister	4	Backing card			56	Box
T4555 1	1	Bag					56	Box
T4555 2	1	Bag					56	Box
T4555-1T	0.6	Blister	4	Backing card			56	Box
T4555-2T	0.6	Blister	4	Backing card			56	Box
T4556 1	1	Bag					56	Box
T4556 2	1	Bag					56	Box
T4556-1T	0.6	Blister	4	Backing card			56	Box
T4556-2T	0.6	Blister	4	Backing card			56	Box
T4557 05	1	Bag					56	Box
T4557 06	1	Bag					56	Box
T4557 07	1	Bag					56	Box
T4557 08	1	Bag					56	Box
T4557 09	1	Bag					56	Box
T4557 10	1	Bag					56	Box
T4557 15	1	Bag					56	Box
T4557 20	1	Bag					56	Box
T4557 25	1	Bag					56	Box
T4557 27	1	Bag					56	Box
T4557 30	1	Bag					56	Box
T4557 40	1	Bag					56	Box
T4557-05T	0.6	Blister	4	Backing card			56	Box
T4557-06T	0.6	Blister	4	Backing card			56	Box

T4557-07T	0.6	Blister	4	Backing card			56	Box
T4557-08T	0.6	Blister	4	Backing card			56	Box
T4557-09T	0.6	Blister	4	Backing card			56	Box
T4557-10T	0.6	Blister	4	Backing card			56	Box
T4557-15T	0.6	Blister	4	Backing card			56	Box
T4557-20T	0.6	Blister	4	Backing card			56	Box
T4557-25T	0.6	Blister	4	Backing card			56	Box
T4557-27T	0.6	Blister	4	Backing card			56	Box
T4557-30T	0.6	Blister	4	Backing card			56	Box
T4557-40T	0.6	Blister	4	Backing card			56	Box
T4557T 10	1	Bag					56	Box
T4557T 15	1	Bag					56	Box
T4557T 20	1	Bag					56	Box
T4557T 25	1	Bag					56	Box
T4557T 30	1	Bag					56	Box
T4557T-10T	0.6	Blister	4	Backing card			56	Box
T4557T-15T	0.6	Blister	4	Backing card			56	Box
T4557T-20T	0.6	Blister	4	Backing card			56	Box
T4557T-25T	0.6	Blister	4	Backing card			56	Box
T4557T-30T	0.6	Blister	4	Backing card			56	Box
T4561 1	0.6	Blister	4	Backing card			56	Box
T4561 2	0.6	Blister	4	Backing card			56	Box
T4561 3	0.6	Blister	4	Backing card			56	Box
T4562 1	0.6	Blister	4	Backing card			56	Box
T4562 2	0.6	Blister	4	Backing card			56	Box
T4562 3	0.6	Blister	4	Backing card			56	Box
T4562 4	0.6	Blister	4	Backing card			56	Box
T4562-215	19	Box					65	Box
T4562-2CB	20	Insert tray	88	Box			56	Box
T4579-1T	0.6	Blister	4	Backing card			56	Box
T4579-2T	0.6	Blister	4	Backing card			56	Box