

# PRODUCT SPECIFICATION

<b>Brand</b>	C.K
<b>Product Range</b>	Screwdriver bit drivers
<b>Catalogue number</b>	4564, 4565, 4570, 4581
<b>Date</b>	26/09/2008

## Range Description

A range of professional quality screwdriver bit drivers

## Features

### 4570

- Magnetic bit holder with high strength stainless steel bit holder
- Hex drive
- Drive conforms to DI3126 C6,3 & ISO 1173

### 4564

- Magnetic bit holder with high strength stainless steel bit holder
- SDS Plus drive

### 4564E

- Locking bit holder positively locks the bit in place
- Collar release mechanism for quick bit changes
- Spinning collar can be held in use for extra control
- Drive conforms to DI3126 C6,3 & ISO 1173

### 4565

- Automatic magnetic docking between bit and screw for repetitive screw driving
- Spinning collar can be held in use for extra control
- Drive conforms to DI3126 C6,3 & ISO 1173

### 4581

- Screwdriver with 6mm hex drive end for screwdriver bits
- Shatterproof wipe clean handle
- Hex shaft for strength



Item Number	Item Description	EAN No	Commodity code	Carton Qty
T4564EC	Screwdriver Bit Holder Hex Drive Locking Carded	5013969986952	82054000	20
T4564SDSC	Screwdriver Bit Holder SDS Drive Magnetic Carded	5013969975239	82054000	20
T4565	Screwdriver Bit Holder for driving screws Carded	5013969984972	82054000	100
T4570	Screwdriver Bit Holder S/S Hex drive Carded	5013969820300	82054000	100
T4581	Bit Holder Hand 4581	5013969978933	82054000	6

Technical product information	
Standards compliance	
User health and safety information	
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K screwdriver bit drivers are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Germany

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T4564EC	18	18	60	32	48	18	145	40
T4564SDSC	10	10	85	46	48	12	145	50
T4565	18	18	60	24	48	18	145	54
T4570	9	9	60	22	48	12	145	24
T4581	25	25	250	120	35	28	285	124

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T4564EC	95	330	60	905		
T4564SDSC	95	330	60	1105		
T4565	180	390	100	5620		

T4570	180	390	100	2620		
T4581	310	140	35	755		

### Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T4564EC	4	Blister	4	Backing card			Box	90
T4564SDSC	1	Blister	4	Backing card			Box	90
T4565	2	Blister	4	Backing card			Box	220
T4570	2	Blister	4	Backing card			Box	220
T4581	4	Hanger			10	Bag		