

VQC Ceiling Speakers




The VQC range of 100v ceiling speakers are designed for quick and easy installation. Suitable for paging & background music applications into schools, offices & retail premises.


- Designed for quick installation
- High quality speaker drivers
- 100V Line transformers with multi-taps
- Slim profile with flush fitting grille
- Metal driver chassis & grille
- Supplied with cutting guides




VQC8



VQC6



VQC5



Specifications

| | VQC5 | VQC6 | VQC8 |
|---------------------|---------------|---------------|---------------|
| Driver Size | 5.25" | 6.5" | 8" |
| Power (RMS @ 8Ω) | 30W | 40W | 50W |
| 100V Tappings | 8W, 4W, 2W | 8W, 4W, 2W | 10W, 5W, 2.5W |
| Freq Response | 165Hz - 20kHz | 125Hz - 20kHz | 97Hz - 20kHz |
| Driver Impedance | 8Ω | 8Ω | 8Ω |
| SPL (1W/1m) | 84dB | 85dB | 90dB |
| Dimensions (mm) | 160 x 83 | 200 x 68 | 265 x 84 |
| Cut Out Dia. (mm) | 136 | 168 | 230 |
| Mounting Depth (mm) | 80 | 60 | 75 |
| Weight | 500g | 760g | 1.34kg |