



## VCS Column Speakers



The VCS range of column speakers are designed for quick and easy installation into 100V or low impedance systems. Suitable for speech & background music applications into houses of worship, schools, offices & retail premises.

- Designed for quick installation
- Vertically stacked 2.5" speaker drivers
- Built-in 100V Line transformers with multi-taps
- Rotary selector for tappings
- Extruded aluminium casing with plastic end caps
- Coated metal grille
- Supplied with mounting brackets



Specifications		
	VCS12	VCS20
Drivers	4x 2.5"	8x 2.5"
Power (RMS/Max)	16W/32W @ 8Ω	32W/64W @ 4Ω
100V Tappings	12W, 6W, 3W, 1.5W	20W, 10W, 5W, 2.5W
Other Tappings	Off & 8Ω	Off & 4Ω
Freq Response	200Hz - 16kHz	200Hz - 16kHz
SPL (1W/1m)	91dB	93dB
Dispersion Angle	160° (Transverse)	160° (Transverse)
Dimensions (mm)	105 x 410 x 90	105 x 620 x 90
Weight	2.3kg	3.6kg