

Logitech®

Wireless Solar Keyboard K750

The solar-powered keyboard that makes battery hassles a thing of the past

- Powered by light
- Sleek, minimalist design - only 7.5 mm thick
- Feel-good typing
- Logitech® Advanced 2.4 GHz wireless connectivity
- Logitech® Unifying receiver

Battery hassles are a thing of the past with the solar-powered Logitech® Wireless Solar Keyboard K750. It charges itself whenever there's light, so you can say goodbye to batteries, power bricks and charging cables. And from the PVC-free construction to the fully recyclable box, this keyboard is designed to minimise its footprint. With sleek lines and a thin profile, this stylish, streamlined keyboard adds style to your workspace. Combining the best of traditional keyboards, laptops and a Logitech-only concave key cap design, you'll enjoy faster, quieter, feel-good typing - hour after hour. Plus, you'll get Logitech® Advanced 2.4 GHz wireless and the tiny Logitech® Unifying receiver.





Logitech

Logitech®

Wireless Solar Keyboard K750

Package specification

	Primary pack	Master shipper carton
Part # EWR2	Multiple	n/a
Bar code	Multiple	Multiple
Weight	1068.5 g	4.695 kg
Length	48.50 cm	49.50 cm
Width	3.50 cm	15.20 cm
Height/depth	20.00 cm	21.60 cm
Volume	3.395dm ³	0.01625m ³
1 primary pack	1	n/a
1 intermediate pack	0	n/a
1 master shipper carton	4	1
1 pallet EURO	396	99
1 container 20 ft	6960	1740
1 container 40 ft	14640	3660
1 container 40 ft HQ	17568	4392

Package contents

- Keyboard
- Logitech Unifying receiver
- Wireless extender
- Cleaning cloth
- 3-year manufacturer's guarantee and full product support
- User documentation printed on the inside of the box.

System requirements

- Windows-based PC
- Windows® XP, Windows Vista® or Windows® 7
- Light source from sunlight and/or indoor lighting

920-002915 French
 920-002916 German
 920-002917 Swiss
 920-002919 Italian
 920-002920 Portuguese
 920-002921 Spanish

920-002922 Danish
 920-002923 Norwegian
 920-002924 Swedish
 920-002927 Belgian
 920-002929 UK English
 920-002931 Turkish

920-002932 Intl NSEA
 920-002934 Czech
 920-002936 Hungarian
 920-002938 Russian
 920-002942 Intl EER

