

## 2 Port Industrial USB to Serial RJ45 Adapter - Wallmount and DIN Rail

StarTech ID: ICUSB2322RJ



The ICUSB2322RJ 2-Port Industrial USB to Serial RJ45 Adapter (Wallmount and DIN Rail) allows you to add two RS232 serial connections using RJ45 signaling ports to a PC or Server through a single USB 2.0 port.

The RS232 to RJ45 adapter features COM port retention to maintain your port number assignments across a reboot and supports serial data rates up to 921 Kbps. The included DIN Rail clips (Top Hat) and wall-mounting brackets provide simple solutions for out of the way installations, while the sturdy metal enclosure offers durability in harsh industrial environments.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications

- Perfect for IT Administrators looking to add legacy functionality to newer laptops, PCs and servers that lack integrated RS232
- Connect, monitor and control industrial/automotive sensors and equipment

### Features

- Adds 2 RS232 serial RJ45 connectors via a single USB port
- Includes wallmount and Top-Hat DIN rail mounting brackets
- Supports data rates up to 921.6 Kbps
- COM Port retention
- USB-Powered - No external adapter required
- USB 2.0 High Speed (480Mbps) and Full Speed (12Mbps) supported
- USB connection features optional latching female screw holes for added security

Technical Specifications

Warranty	2 Years
Interface	Serial
Ports	2
Bus Type	USB 2.0
Port Style	External Hub
Chipset ID	FTDI - FT232R
Connector Type(s)	1 - USB B (4 pin) Female
Connector Type(s)	2 - RJ-45 Female
FIFO	128 Bytes
Serial Protocol	RS-232
Max Baud Rate	921.6 Kbps
Data Bits	7, 8
Parity	Odd, Even, Mark, Space, None
Stop Bits	1, 2
OS Compatibility	Windows® 8 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64), 2000, 98SE, CE (4.2+) Windows® Server 2012, 2008 R2, 2003(32/64), 2000 Mac OS® 10.x (Tested up to 10.9) Linux
Color	Black
Enclosure Type	Steel
Product Length	65 mm [2.6 in]
Product Width	42 mm [1.7 in]
Product Height	20 mm [0.8 in]
Product Weight	78 g [2.8 oz]
Humidity	5~95% RH
Operating Temperature	0°C to 55°C (32°F to 131°F)
Storage Temperature	-20°C to 85°C (-4°F to 185°F)
Shipping (Package) Weight	0.3 kg [0.6 lb]
Included in Package	1 - 2 Port USB to Serial RJ45 Adapter
Included in Package	1 - Wallmount Bracket
Included in Package	2 - DIN Rail Clips
Included in Package	1 - USB A to B Cable
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

