

## 2 Port USB HDMI® Cable KVM Switch with Audio and Remote Switch – USB Powered

StarTech ID: SV211HDUA



The SV211HDUA 2-Port HDMI® Cable KVM Switch with Audio and Remote Switching Control lets you control two HDMI, USB equipped PCs with a single monitor, keyboard, mouse and audio peripheral set.

To help organize your desk without sacrificing work space, this compact HDMI USB KVM features integrated cables that can be connected directly to your system, while leaving a minimal footprint. The switch features a remote push-button on a 1.5 meter (5ft) integrated cable that can be placed in an easily accessible location, as well as keyboard hot-keys, and PC or Mac® compatible software for switching between systems. To eliminate the need for a bulky external power adapter and wall outlet, the HDMI KVM switch is USB-powered.

This KVM with HDMI video capability offers support for 1080p HD resolutions (up to 1920x1200) for the ability to drive a large HDMI display for applications that require high graphical output.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications

- Great for PC test/burn-in computer control, saving the desk space required for two monitors, keyboards and mice
- Perfect for sharing computers and attached peripherals in the home or home office
- Dual system control for single user workstations increasing user productivity in the office

## Features

- Supports HD resolutions (1080p - 1920x1200)
- Switch PCs via push-button, hot-keys or switching software
- Space-saving design, minimal footprint
- Integrated KVM cables and remote switch
- Switching software supports PC and Mac® platforms
- USB Powered - No external power adapter required
- Independent audio/mic switching for uninterrupted audio
- Analog (3.5mm) and HDMI audio supported
- Supports hot-plugging
- Remote switch on 1.5m (5ft.) cable

**Technical Specifications**

Warranty	2 Years
Audio	Yes
Cables Included	Yes
Daisy-Chain	No
Industry Standards	HDCP
KVM Ports	2
Multi-Monitor	No
PC Interface	USB
PC Video Type	HDMI
Rack-Mountable	No
Console Interface(s)	1 - HDMI (19 pin) Female
Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position) Female
Console Interface(s)	2 - USB A (4 pin) Female
Host Connectors	1 - HDMI (19 pin) Male
Host Connectors	1 - USB A (4 pin) Male
Host Connectors	2 - 3.5 mm Mini-Jack (3 Position) Male
Audio Specifications	3.5mm and HDMI audio supported
IP Control	No
Port Selection Support	Push Button, Hotkeys, and Software
OS Compatibility	Windows® 8 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64), 2000 Windows Server 2012, 2008 R2, 2003(32/64) Mac OS 10.x (Tested up to 10.9), 9.x
<b>Note</b>	OS Compatibility refers to KVM software only - the KVM itself can be used without software on any platform
Cable Length	850 mm [33.5 in]
Color	Black
Enclosure Type	Plastic
Product Height	23 mm [0.9 in]
Product Length	88 mm [3.5 in]
Product Weight	356 g [12.6 oz]
Product Width	66 mm [2.6 in]
LED Indicators	1 - PC Selection indicator
Humidity	0~90% RH Non-Condensing
Operating Temperature	0°C to 40°C (32°F to 104°F)
Storage Temperature	-20°C to 60°C (4°F to 140°F)

Shipping (Package) Weight	465 g [16.4 oz]
Included in Package	1 - KVM Switch
Included in Package	1 - Software CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

