



GE
Lighting



Single Ended Halogen T27 230-240V

88469

Product information

Quartzline® lamps designed for optimum performance in today's precision range of stage, studio and architectural luminaires. Full range up to 24,000 W
-Range of bases to meet the needs of OEMs -
Chromised seal protection up to 500° C.



Product data

Cap/Base	GY9.5
Bulb Shape	Tubular
Bulb Diameter [mm]	23
Maximum Overall Length [mm]	89
Light Center Length [mm]	46.5
Net weight per piece [g]	24
Gross weight per piece [g]	35
Brand	General Electric (GE)

Performance data

Colour Rendering Index (CRI) [Ra]	100
Nominal correlated colour temperature (CCT) [K]	3050
Nominal lumens [lm]	14500
Energy efficiency class (EEC)	C
Rated Life [h]	400
Nominal power [W]	650
Nominal lamp voltage [V]	230

Electrical data

Weighted energy consumption [kWh/1000h]	648.58
Coil type	C-13D
Dimming Capability	Yes
Ballast Required	No

Logistic data

DUN Code	10043168884690
EAN Code	0043168884693
Pack Quantity	24
Layer quantity	504 EUR, 600 UK
Layer quantity EUR	504
Layer quantity UK	600
Pallet quantity EUR (PC)	4032
Pallet quantity UK (PC)	4800
Outer case size	170 x 255 x 130 (mm)
Product status	Available

Application areas



Film and Broadcast



Theatre

Downloads & Links

[Go to the catalog site \(HTTP\)](#)[Entertainment Solution Spectrum Catalogue \(PDF\)](#)[Lighting design tools & calculators \(HTTP\)](#)

Disclaimer

Special Purpose Lamp, Not suited for household illumination