



GE  
Lighting



Spiral T2 - 8,000 / 10,000  
hours

OT&FLE12HLX/T2/827/B22 1/6T GE 10Y  
/01

**72716**

---

## Product information

The T2 10,000 hours spiral lamps are one of the most popular bulb shapes in the energy saving category. With its small size, it will fit all applications currently using incandescent bulbs. Providing more light than the original stick lamps, spiral lamps are one of the most eco-friendly energy saving solutions available today.

---



## Product data

Cap/Base	B22d
Bulb Shape	Heliax
Bulb Diameter [mm]	10
Bulb maximum overall diameter [mm]	53
Nominal Length [mm]	99
Maximum Overall Length [mm]	544
Net weight per piece [g]	53
Gross weight per piece [g]	91
Operating position	U - Universal
Mercury Content [mg]	0.85
UV radiance	exempt
Regulatory comment	EUP related
Brand	General Electric (GE)

## Performance data

Colour Code	827
Colour Rendering Index (CRI) [Ra]	80
Nominal correlated colour temperature (CCT) [K]	2700
Nominal lumens [lm]	715
Energy efficiency class (EEC)	A
Rated Life [h]	10000
Nominal power [W]	12
Nominal lamp voltage [V]	230

## Electrical data

Weighted energy consumption [kWh/1000h]	12
Lamp Current [A]	110
Operating Temperature (MIN) [°C]	-10
Operating Temperature (MAX) [°C]	50
Starting ambient temperature range	-10
Startup time [sec]	0.8
Dimming Capability	No


## Logistic data

DUN Code	30043168727168
EAN Code	0043168727167
Pack Quantity	6
Inner pack type	BOX
Outer pack type	OUTER BOX
Layer quantity	198 EUR, 258 UK
Layer quantity EUR	198
Layer quantity UK	258
Pallet quantity EUR (PC)	1584
Pallet quantity UK (PC)	2064
Outer case size	194 x 138 x 133 (mm)
Product status	Available

## Application areas



## Survival Data



## Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[CFL Integrated Spectrum Catalogue \(PDF\)](#)

[Spiral T2 10000 and 8000 Hrs Data sheet \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

[Disposing and Cleaning of CFL Lamps \(HTTP\)](#)