

Digital Optical Cable, Braided

CABLE
POWER



The Aluminium Optical Cable is a high performing Toslink cable with a robust aluminium head shell.

Braided for durability, it offers the highest resolution available, and the most accurate digital audio signal transfer for maximum audio

PRODUCT FEATURES:

- Available lengths: 2m, 3m, 5m
- Highest resolution Toslink Cable offers the most accurate digital audio signal transfer for maximum audio clarity and resolution
- Precision polished end-face for optimal coupling
- Spring strain relief protects optical fibre during bending
- Delivers the most accurate bitstream transfer for the clearest and smoothest sound from your digital audio device
- Ultra flexible PVC jacket construction makes installation very easy even in hard to reach areas
- OD – 5.0mm with RoHS PVC jacket
- 24k gold plated copper connector for best connectivity and signal protection
- Nitrogen gas injected di-electric vibration absorption insulation to reduce digital jitter
- PE bag for protection from abrasion
- Hoodcover to keep from dust
- IN STOCK FOR IMMEDIATE FREE DELIVERY

Part numbers

2 metres	CPOP002-2m
3 metres	CPOP002-3m
5 metres	CPOP002-5m