


APA Series Power Amplifiers



The APA series of power amplifiers are designed for mobile and small installation applications. With its choice of input and output connectors, 2U chassis and switchable mains power input, these amplifiers will cover most situations and also makes an ideal backup amplifier for when the unmentionable happens.



- Available in 200W, 500W & 800W.
- Rotary gain controls.
- Signal, Clip & Protect LED indicators.
- Output circuit overload protection.
- Fan cooling.
- 19" 2U Rack mountable.
- IEC mains input with voltage selector switch.
- Inputs: Combo XLR/Jack & RCA.
- Outputs: Jacks, Binding posts & Locking speaker connectors.

Specifications			
	APA200	APA500	APA800
Output Per Ch. @ 4Ω (RMS/Max)	100W/200W	250W/500W	400W/800W
Output Per Ch. @ 8Ω (RMS/Max)	70W/140W	170W/340W	270W/540W
Freq Response	20Hz - 20kHz	20Hz - 20kHz	20Hz - 20kHz
Signal to Noise Ratio	90dB	90dB	90dB
Mains Power (switchable)	110V 60Hz / 240V 50Hz	110V 60Hz / 240V 50Hz	110V 60Hz / 240V 50Hz
Dimensions (mm)	482 x 88 x 270	482 x 88 x 340	482 x 88 x 340
Weight	6.8kg	9.1kg	12.3kg