



APB Series Power Amplifiers



The APB series of power amplifiers are designed for large mobile and installation applications. With its choice of input sensitivity, output modes, 2U chassis and ability to run down to 2 Ohms per channel, these amplifiers will cover the majority of your audio application needs.



- Available in 1400W, 2100W & 2700W.
- Class H amplifiers.
- Rotary gain controls.
- Signal, Clip & Protect LED indicators.
- Bridged & Parallel mode LED indicators.
- Switchable sensitivity with clip limiter.
- Switchable ground lift.
- Switchable output modes: Parallel, Stereo & Bridged.
- Short circuit, DC, overload & thermal protection.
- Dual fan cooling.
- 19" 2U Rack mountable.
- Inputs: XLR (with parallel XLR link outs).
- Outputs: Binding posts & Locking speaker connectors.

Specifications

	APB1400	APB2100	APB2700
Output Per Ch. @ 2Ω (RMS)	1000W	1400W	1800W
Output Per Ch. @ 4Ω (RMS)	700W	1050W	1350W
Output Per Ch. @ 8Ω (RMS)	400W	600W	800W
Output Bridged @ 4Ω (RMS)	1700W	2300W	2900W
Output Bridged @ 8Ω (RMS)	1250W	1750W	2300W
Freq Response	5Hz - 50kHz	5Hz - 50kHz	5Hz - 50kHz
Signal to Noise Ratio	>105dB	>105dB	>105dB
THD	0.05%	0.05%	0.05%
Dimensions (mm)	482 x 88 x 453	482 x 88 x 453	482 x 88 x 453
Weight	22.5kg	25kg	26kg