

APS Active Series



The APS range of active ABS moulded PA speakers cabinets are designed to be lightweight for multi-purpose sound reinforcement. The APS active range are suitable for most applications from small church halls to schools, bars and clubs.

- 8", 10", 12" & 15" PA Speakers
- Lightweight moulded ABS enclosures
- Protective front grille
- Titanium compression driver
- Convection cooling
- 35mm internal pole-mounting
- Separate mic and line inputs
- Controls: Mic, Line, Master volume, Bass & Treble.
- Line out for linking multiple speakers
- IEC mains input with dual voltage selector switch.

Specifications

	APS8A	APS10A	APS12A	APS15A
Driver Size	8"	10"	12"	15"
Tweeter Size	25mm	34mm	34mm	44mm
Driver Power (RMS/Max)	100W / 200W	120W / 250W	180W / 350W	200W / 400W
Amp Power (RMS)	80W	100W	150W	180W
Freq Response (-10dB)	65Hz - 18kHz	55Hz - 18kHz	50Hz - 18kHz	40Hz - 18kHz
Impedance	4Ω	4Ω	4Ω	4Ω
SPL	92dB	94dB	96dB	98dB
Mic Inputs	Jack/XLR	Jack/XLR	Jack/XLR	2x Jack/XLR
Line Inputs	RCA/XLR	RCA/XLR	RCA/XLR	RCA/XLR
Line Outputs	Jack	Jack/XLR	Jack/XLR	Jack/XLR
Weight	7.5kg	12.5kg	17kg	21kg
Dimensions (mm)	340 x 480 x 280	410 x 555 x 325	465 x 664 x 375	530 x 760 x 465
Weight	7.5kg	12.5kg	17kg	22kg