



STC 40 Transformer



- Selectable output voltage.
- Over Heat Protection (OHP) and Over Current Protection (OCP) protect driver from damage or malfunction.
- Temperature Detection powers down the unit and resets automatically when unit restores to acceptable levels.
- Switchable 110V & 230V input voltage. Unit will reset itself if motor/current overload is too high.
- Start & Stop Signal Output (for PLC).
- Screwdriver Lock Signal Input (for PLC).
- Unit can be connected to the Scout (Screw Counter).

Specifications:

Max. Output: 10A

Output VDC: 30/40V

Input VAC: 110/230V

Size inches (W x D x H): 4 3/8" x 7 1/2" x 2 3/8"

Weight: 1.8 lbs.

Model: STC40 for LF-Series, BF-Series and NF-Series

Item # 145754