


FEATURES

- Non-Polarized
- 24 Volt DC Operation
- 12V AC or DC Operation
- CRI ≥ 80 (WW)
- ≥ 70 (CW)



SPECIFICATIONS

PARAMETERS	SYMBOL	VALUES			UNIT
		MIN	TYP	MAX	
Input Voltage	Vin	10	12	30	VDC
Input Current (Bright)	Iin	0.02	0.05	0.07	A
Power Consumption (MAX)	P	0.6			W
CRI	Ra	≥ 80 (Warm White) / ≥ 70 (Cool White)			
Product Life	H	50000			Hr
CCT	--	3000 (Warm White) / 6000 (Cool White)			K
Lumunous Flux (MAX)	Φ	55-65 (Warm White) 65-75 (Cool White)			Lm
Operating Temperature	Topr	-20	25	40	$^{\circ}$ C

ACCESSORIES

SOCKET: 2910F-47

JKL PART NUMBERS: LE-3042-02-CW and LE-3042-02-WW

		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- REF. 2 PL +/- REF. ANGLE +/-		JKL COMPONENTS CORPORATION			
				TITLE NON-POLARIZED 360 DEGREES LED FESTOON LAMP			
A	ADD FEATURES/ACCESS, CHNG SPEC	11/4/13	APPV'D BY	DATE	SIZE	FSCM NO.	DRAWING NO.
	RELEASED	10/8/13	L. WENGSTROM	11/4/13	A	55335	LE-3042-02 MULTI
		- CAD DRAWING -		SCALE	RELEASED DATE	REVISION DATE	REV. NO.
		MANUAL REVISIONS NOT PERMITTED		NONE	10/8/13	11/4/13	A
REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE					SHEET 1 OF 1