



TSSH-115-01-L-D



TSSH-120-01-L-DH

TSSH SERIES

(2,54 mm) .100"

SHROUDED .025" SQ POST HEADERS

Mates with:
SSW, SSQ, SSM, SMSD

Important Note:
This Series will only mate with SSW, SSQ, SSM & SMSD Series

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com/TSSH

Insulator Material:
Black Liquid Crystal Polymer

Terminal Material:
Phosphor Bronze

Plating:

Au or Sn over 50µ" (1,27 µm) Ni

Operating Temp Range:
-55°C to +105°C with Tin;
-55°C to +125°C with Gold

RoHS Compliant:
Yes

Processing:

Lead-Free Solderable:
Yes

SMT Lead Coplanarity (-DV):
(0,10 mm) .004" max (05-10)
(0,15 mm) .006" max (15-20)
(0,20 mm) .008" max (25-36)

SMT Lead Coplanarity (-DH):
(0,15 mm) .006" max

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality




APPLICATIONS



ALSO AVAILABLE (MOQ Required)

- Other platings
- Contact Samtec.

Note: Some lengths, styles and options are non-standard, non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice.