



Nano-Change® (M8) Multi-Port Splitter Boxes

4 pole – Twin I/O Multi-Ports

Function	Cable Colour	M16 Connector Pin No	Function	Cable Colour	M16 Connector Pin No	Function	Cable Colour	M16 Connector Pin No	Function	Cable Colour	M16 Connector Pin No
+V	Brown	A									
0V	Blue	L									
Port 1 P4	White	U	Port 6 P4	Red	N	Port 1 P2	Grey/Pink	P	Port 6 P2	Yellow/Brown	C
Port 2 P4	Green	J	Port 7 P4	Black		Port 2 P2	Red/Blue	S	Port 7 P2	White/Grey	
Port 3 P4	Yellow	M	Port 8 P4	Violet		Port 3 P2	White/Green	T	Port 8 P2	Grey/Brown	
Port 4 P4	Grey	R	Port 9 P4	White/Blue		Port 4 P2	Brown/Green	G	Port 9 P2	White/Pink	
Port 5 P4	Pink	O	Port 10 P4	Brown/Blue		Port 5 P2	White/Yellow	E	Port 10 P2	Pink/Brown	



Cable Length (m)









Integral End Cable Entry

4 Port

6 Port

8 Port

10 Port



PUR	Length (m)	4 Port	6 Port	8 Port	10 Port
	5.0	BEY403P-FBP-05	BEY603P-FBP-05	BEY803P-FBP-05	BEYA03P-FBP-05
	10.0	BEY403P-FBP-10	BEY603P-FBP-10	BEY803P-FBP-10	BEYA03P-FBP-10
	20.0	BEY403P-FBP-20	BEY603P-FBP-20	BEY803P-FBP-20	BEYA03P-FBP-20









Integral Top Cable Entry

4 Port

6 Port

8 Port

10 Port







PUR	Length (m)	4 Port	6 Port	8 Port	10 Port
	5.0	BNY403P-FBP-05	BNY603P-FBP-05	BNY803P-FBP-05	BNYA03P-FBP-05
	10.0	BNY403P-FBP-10	BNY603P-FBP-10	BNY803P-FBP-10	BNYA03P-FBP-10
	20.0	BNY403P-FBP-20	BNY603P-FBP-20	BNY803P-FBP-20	BNYA03P-FBP-20

Integral M16 Home Run Connector

4 Port

6 Port



See bottom of page 7 for connectors

BNY403P-FBC

BNY603P-FBC