



CONNECTORS, CORDSETS AND DISTRIBUTION BOXES FOR SENSOR AND ACTUATOR CONNECTIVITY APPLICATIONS

IN-LINE SPLITTERS FOR M12 DISTRIBUTION BOXES - Order Number

MICRO-CHANGE® (M12) TO NANO-CHANGE® (M8) IN-LINE SPLITTERS (MALE / 2X FEMALE)

Length (m)	MALE STRAIGHT / FEMALE STRAIGHT			MALE STRAIGHT / FEMALE 90°		
	PVC	PUR/PVC	PUR	PVC	PUR/PVC	PUR
0.6	484A30E02M006	484A30P02M006	484A30H08M006	484A31E02M006	484A31P02M006	484A31H08M006
1.0	484A30E02M010	484A30P02M010	484A30H08M010	484A31E02M010	484A31P02M010	484A31H08M010
2.0	484A30E02M020	484A30P02M020	484A30H08M020	484A31E02M020	484A31P02M020	484A31H08M020
3.0	484A30E02M030	484A30P02M030	484A30H08M030	484A31E02M030	484A31P02M030	484A31H08M030
4.0	484A30E02M040	484A30P02M040	484A30H08M040	484A31E02M040	484A31P02M040	484A31H08M040
5.0	484A30E02M050	484A30P02M050	484A30H08M050	484A31E02M050	484A31P02M050	484A31H08M050
10.0	484A30E02M100	484A30P02M100	484A30H08M100	484A31E02M100	484A31P02M100	484A31H08M100

Length (m)	MALE STRAIGHT / FEMALE PNP LED 90°		
	PVC	PUR/PVC	PUR
0.6	484AP7E02M006	484AP7P02M006	484AP7H08M006
1.0	484AP7E02M010	484AP7P02M010	484AP7H08M010
2.0	484AP7E02M020	484AP7P02M020	484AP7H08M020
3.0	484AP7E02M030	484AP7P02M030	484AP7H08M030
4.0	484AP7E02M040	484AP7P02M040	484AP7H08M040
5.0	484AP7E02M050	484AP7P02M050	484AP7H08M050
10.0	484AP7E02M100	484AP7P02M100	484AP7H08M100

MICRO-CHANGE® (M12) TO MICRO-CHANGE® (M12) IN-LINE SPLITTERS (MALE / 2X FEMALE)

Length (m)	MALE STRAIGHT / FEMALE STRAIGHT			MALE STRAIGHT / FEMALE 90°		
	PVC	PUR/PVC	PUR	PVC	PUR/PVC	PUR
0.6	884A30E03M006	884A30P03M006	884A30H09M006	884A31E03M006	884A31P03M006	884A31H09M006
1.0	884A30E03M010	884A30P03M010	884A30H09M010	884A31E03M010	884A31P03M010	884A31H09M010
2.0	884A30E03M020	884A30P03M020	884A30H09M020	884A31E03M020	884A31P03M020	884A31H09M020
3.0	884A30E03M030	884A30P03M030	884A30H09M030	884A31E03M030	884A31P03M030	884A31H09M030
4.0	884A30E03M040	884A30P03M040	884A30H09M040	884A31E03M040	884A31P03M040	884A31H09M040
5.0	884A30E03M050	884A30P03M050	884A30H09M050	884A31E03M050	884A31P03M050	884A31H09M050
10.0	884A30E03M100	884A30P03M100	884A30H09M100	884A31E03M100	884A31P03M100	884A31H09M100

Length (m)	MALE STRAIGHT / FEMALE PNP LED STRAIGHT			MALE STRAIGHT / FEMALE PNP LED 90°		
	PVC	PUR/PVC	PUR	PVC	PUR/PVC	PUR
0.6	884AP6E03M006	884AP6P03M006	884AP6H09M006	884AP7E03M006	884AP7P03M006	884AP7H09M006
1.0	884AP6E03M010	884AP6P03M010	884AP6H09M010	884AP7E03M010	884AP7P03M010	884AP7H09M010
2.0	884AP6E03M020	884AP6P03M020	884AP6H09M020	884AP7E03M020	884AP7P03M020	884AP7H09M020
3.0	884AP6E03M030	884AP6P03M030	884AP6H09M030	884AP7E03M030	884AP7P03M030	884AP7H09M030
4.0	884AP6E03M040	884AP6P03M040	884AP6H09M040	884AP7E03M040	884AP7P03M040	884AP7H09M040
5.0	884AP6E03M050	884AP6P03M050	884AP6H09M050	884AP7E03M050	884AP7P03M050	884AP7H09M050
10.0	884AP6E03M100	884AP6P03M100	884AP6H09M100	884AP7E03M100	884AP7P03M100	884AP7H09M100

Options: NPN format LED indication, choice of cable and coupling materials