

## General Information

Extended Product Type:	316P6W
Product ID:	2CMA166476R1000
EAN:	7392696664769
Catalog Description:	Plug, 6h, 16A, IP67, 3P+E
Long Description:	Plug, earthing sleeve position 6h, rated current 16A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Red

## Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Plugs

## Ordering

EAN:	7392696664769
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

## Dimensions

Product Net Width:	79 mm
Product Net Height:	79 mm
Product Net Length:	144 mm
Product Net Depth:	79 mm
Product Net Weight:	0.24 kg

## Container Information

Package Level 1 Width:	84 mm
Package Level 1 Length:	167 mm
Package Level 1 Height:	85 mm
Package Level 1 Gross Weight:	0.24 kg
Package Level 1 EAN:	7392696664769
Package Level 1 Units:	1 piece

## Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	<a href="#">2CMC700005D0001;</a>
Environmental Information:	<a href="#">2CMC700001D0002;</a>
RoHS Information:	<a href="#">2CMC700047D0001;</a>

## Additional Information

Additional Information:	Cable entry compression gland
Cable Cross-Section:	1.0 ... 2.5 mm <sup>2</sup>
Color:	Red
Degree of Protection:	acc. to IEC 60529 IP67
Enclosure Material:	Thermoplastic polyester (PBT)
Frequency (f):	50 Hz 60 Hz
Function:	Plug
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#316P6W
Number of Poles:	4
Object Classification Code:	2CMT005069
Product Main Type:	P
Product Name:	Industrial Plug
Protection Type:	Watertight
Rated Current (I <sub>n</sub> ):	16 A
Rated Voltage (U <sub>r</sub> ):	380 ... 415 V
RoHS Date:	2009-01
Standards:	IEC 60309-1,-2
Suitable For:	Plugs
Suitable for Product Class:	Industrial Plugs and Sockets

## Classifications

E-nummer:

2416245

UNSPSC:

39120000

