

### General Information

Extended Product Type:	216C6W
Product ID:	2CMA166538R1000
EAN:	7392696665384
Catalog Description:	Connector, 6h, 16A, IP67, 2P+E
Long Description:	Connector, earthing sleeve position 6h, rated current 16A, IP67 watertight, 2-poles+earth, frequency 50-60 Hz, color code Blue

### Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Connectors

### Ordering

EAN:	7392696665384
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

### Dimensions

Product Net Width:	80 mm
Product Net Height:	80 mm
Product Net Length:	151 mm
Product Net Depth:	80 mm
Product Net Weight:	0.244 kg

### Container Information

Package Level 1 Width:	84 mm
Package Level 1 Length:	167 mm
Package Level 1 Height:	85 mm
Package Level 1 Gross Weight:	0.28 kg
Package Level 1 EAN:	7392696665384
Package Level 1 Units:	1 piece

### Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

### Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	<a href="#">2CMC700005D0001;</a>
Environmental Information:	<a href="#">2CMC700001D0002;</a>
RoHS Information:	<a href="#">2CMC700047D0001;</a>

### Additional Information

Additional Information:	Cable entry compression gland
Cable Cross-Section:	1.0 ... 2.5 mm <sup>2</sup>
Color:	Blue
Degree of Protection:	acc. to IEC 60529 IP67
Enclosure Material:	Thermoplastic polyester (PBT)
Frequency (f):	50 Hz 60 Hz
Function:	Connector
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#216C6W
Number of Poles:	3
Object Classification Code:	2CMT005069
Product Main Type:	C
Product Name:	Industrial Connector
Protection Type:	Watertight
Rated Current (I <sub>n</sub> ):	16 A
Rated Voltage (U <sub>r</sub> ):	200 ... 250 V
RoHS Date:	2009-01
Standards:	IEC 60309-1,-2
Suitable For:	Connectors
Suitable for Product Class:	Industrial Plugs and Sockets

### Classifications

E-nummer:

2416361

UNSPSC:

39120000

