

General Information

Extended Product Type:	232MVS4W
Product ID:	2CMA167870R1000
EAN:	7392696678704
Catalog Description:	Switched interlocked socket-outlet, 4h, 32A, IP67, 2P+E
Long Description:	Switched Interlocked Socket Outlet, vertical, earthing sleeve position 4h, rated current 32A, IP67 watertight, 2-poles+earth, frequency 50-60 Hz, color code Yellow

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Switched Interlocked Socket Outlets, Vertical

Ordering

EAN:	7392696678704
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	120 mm
Product Net Height:	253 mm
Product Net Length:	149 mm
Product Net Depth:	253 mm
Product Net Weight:	0.69 kg

Container Information

Package Level 1 Width:	124 mm
Package Level 1 Length:	337 mm
Package Level 1 Height:	153 mm
Package Level 1 Gross Weight:	0.754 kg
Package Level 1 EAN:	7392696678704
Package Level 1 Units:	1 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1
--------------	---------------------------------------------------------------------------------------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001 ;
Environmental Information:	2CMC700001D0002 ;
RoHS Information:	2CMC700032 ;

Additional Information

Additional Information:	Cable entry, knock-outs Ø25mm
Cable Cross-Section:	2.5 ... 10 mm ²
Cable Entry Position:	Top
Cable Outlets Per Side:	1xØ25
Color:	Yellow
Degree of Protection:	acc. to IEC 60529 IP67
Enclosure Material:	Thermoplastic polyester (PBT)
Frequency (f):	50 Hz 60 Hz
Function:	Switched interlocked socket outlet, vertical
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#232MVS4W
Mounting Type:	Vertical
Number of Poles:	3
Object Classification Code:	2CMT005069
Product Main Type:	MVS
Product Name:	Industrial Switched Interlocked Socket Outlet
Protection Type:	Watertight
Rated Current (I _n):	32 A
Rated Voltage (U _r):	100 ... 130 V
RoHS Date:	2009-01
Standards:	IEC 60 309-1, -2, -4
Suitable For:	Switched Interlocked Socket Outlets, Vertical

Suitable for Product Class: Industrial Plugs and Sockets

Classifications

E-nummer: 2416972
UNSPSC: 39120000

