

## General Information

|                        |   |
|------------------------|---|
| Extended Product Type: | 232MVS6W  |
| Product ID:            | 2CMA167871R1000   |
| EAN:                   | 7392696678711   |
| Catalog Description:   | Switched interlocked socket-outlet, 6h, 32A, IP67, 2P+E   |
| Long Description:      | Switched Interlocked Socket Outlet, vertical, earthing sleeve position 6h, rated current 32A, IP67 watertight, 2-poles+earth, frequency 50-60 Hz, color code Blue |

## Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Switched Interlocked Socket Outlets, Vertical

## Ordering

|                         |                     |
|-------------------------|---------------------|
| EAN:                    | 7392696678711       |
| Minimum Order Quantity: | 1 piece             |
| Country of Origin:      | Czech Republic (CZ) |

## Dimensions

|                     |         |
|---------------------|---------|
| Product Net Width:  | 120 mm  |
| Product Net Height: | 253 mm  |
| Product Net Length: | 149 mm  |
| Product Net Depth:  | 253 mm  |
| Product Net Weight: | 0.69 kg |

## Container Information

|                               |               |
|-------------------------------|---------------|
| Package Level 1 Width:        | 124 mm        |
| Package Level 1 Length:       | 337 mm        |
| Package Level 1 Height:       | 153 mm        |
| Package Level 1 Gross Weight: | 0.754 kg      |
| Package Level 1 EAN:          | 7392696678711 |
| Package Level 1 Units:        | 1 piece       |

## Environmental

|              |   |
|--------------|---|
| RoHS Status: | Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1 |
|--------------|---|

## Certificates and Declarations (Document Number)

|                                 |                                  |
|---------------------------------|----------------------------------|
| Declaration of Conformity - CE: | <a href="#">2CMC700005D0001;</a> |
| Environmental Information:      | <a href="#">2CMC700001D0002;</a> |
| RoHS Information:               | <a href="#">2CMC700032;</a>      |

## Additional Information

|                                  |   |
|----------------------------------|---|
| Additional Information:          | Cable entry, knock-outs Ø25mm                 |
| Cable Cross-Section:             | 2.5 ... 10 mm <sup>2</sup>                    |
| Cable Entry Position:            | Top   |
| Cable Outlets Per Side:          | 1xØ25   |
| Color:                           | Blue  |
| Degree of Protection:            | acc. to IEC 60529 IP67                        |
| Enclosure Material:              | Thermoplastic polyester (PBT)                 |
| Frequency (f):                   | 50 Hz<br>60 Hz                                |
| Function:                        | Switched interlocked socket outlet, vertical  |
| IIT Publishing Status:           | Level 0 - Information enabled                 |
| Invoice Description:             | Ind. P&S#232MVS6W                             |
| Mounting Type:                   | Vertical                                      |
| Number of Poles:                 | 3   |
| Object Classification Code:      | 2CMT005069                                    |
| Product Main Type:               | MVS   |
| Product Name:                    | Industrial Switched Interlocked Socket Outlet |
| Protection Type:                 | Watertight                                    |
| Rated Current (I <sub>n</sub> ): | 32 A  |
| Rated Voltage (U <sub>r</sub> ): | 200 ... 250 V                                 |
| RoHS Date:                       | 2009-01                                       |
| Standards:                       | IEC 60 309-1, -2, -4                          |
| Suitable For:                    | Switched Interlocked Socket Outlets, Vertical |

Suitable for Product Class: Industrial Plugs and Sockets

---

### Classifications

---

E-nummer: 2416973  
UNSPSC: 39120000

---

