

General Information

Extended Product Type:	416PFV6
Product ID:	2CMA168131R1000
EAN:	7392696681315
Catalog Description:	Phase sequence shifter plug, 6h, 16A, IP44, 3P+N+E
Long Description:	Phase sequence shifter plug, 6h, 16A, IP44, 3P+N+E

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Phase Sequence Products

Ordering

EAN:	7392696681315
Minimum Order Quantity:	10 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	76 mm
Product Net Height:	76 mm
Product Net Length:	140 mm
Product Net Depth:	76 mm
Product Net Weight:	0.19 kg

Container Information

Package Level 1 Width:	158 mm
Package Level 1 Length:	138 mm
Package Level 1 Height:	345 mm
Package Level 1 Gross Weight:	0.19 kg
Package Level 1 EAN:	7392696681315
Package Level 1 Units:	1 piece

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001 ;
Environmental Information:	2CMC700001D0002 ;

Additional Information

Additional Information:	Cable entry, compression gland
Cable Cross-Section:	1 ... 2.5 mm ²
Color:	red
Degree of Protection:	IP44
Enclosure Material:	Thermoplastic
Frequency (f):	50 Hz 60 Hz
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	IND. P&S#416PFV6
Number of Poles:	5
Object Classification Code:	2CMT005069
Product Main Type:	PFV
Product Name:	Phase Sequence Shifter
Rated Current (I _n):	16 A
Rated Voltage (U _r):	346 ... 415 V
Standards:	IEC 60 309-2
Suitable For:	416PFV6
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-nummer:	2416193
UNSPSC:	39120000

