

General Information

Extended Product Type:	332RS6W
Product ID:	2CMA167180R1000
EAN:	7392696671804
Catalog Description:	Surface socket-outlet, 6h, 32A, IP67, 3P+E
Long Description:	Surface socket-outlet, earthing sleeve position 6h, rated current 32A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Red

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Surface Socket Outlets

Ordering

EAN:	7392696671804
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	99 mm
Product Net Height:	178 mm
Product Net Length:	129 mm
Product Net Depth:	178 mm
Product Net Weight:	0.43 kg

Container Information

Package Level 1 Width:	144 mm
Package Level 1 Length:	202 mm
Package Level 1 Height:	140 mm
Package Level 1 Gross Weight:	0.6 kg
Package Level 1 EAN:	7392696671804
Package Level 1 Units:	1 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001;
Environmental Information:	2CMC700001D0002;
RoHS Information:	2CMC700022;

Additional Information

Additional Information:	Cable entry Ø 25mm
Cable Cross-Section:	2.5 ... 10 mm ²
Color:	Red
Degree of Protection:	IP67
Enclosure Material:	Thermoplastic polyester (PBT)
Frequency (f):	50 Hz 60 Hz
Function:	Surface socket outlet
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#332RS6W
Number of Poles:	4
Object Classification Code:	2CMT005069
Product Main Type:	RS
Product Name:	Industrial Socket Outlet
Protection Type:	Watertight
Rated Current (I _n):	32 A
Rated Voltage (U _r):	380 ... 415 V
RoHS Date:	2009-01
Standards:	IEC 60309-1,-2
Suitable For:	Surface Socket Outlets
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-nummer: 2416555

UNSPSC: 39120000

