

# CUGT 316

ABB contact for United  
Kingdom



## General Information

<b>Extended Product Type:</b>	CUGT 316
<b>Product ID:</b>	2CMA179301R1000
<b>EAN:</b>	7392696793018
<b>Catalog Description:</b>	Socket-outlet for surface mounting for extra low voltage, 16A, IP44, 3-pole
<b>Long Description:</b>	Socket Outlet Extra low voltage for surface mounting, rated current 16A, IP44 splashproof, 3-poles, frequency 50-60 Hz, color code Purple

## Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets for Extra Low Voltage » Surface Socket Outlets

## Ordering

<b>EAN:</b>	7392696793018
<b>Minimum Order Quantity:</b>	10 piece
<b>Country of Origin:</b>	Germany (DE)

## Dimensions

<b>Product Net Width:</b>	70 mm
<b>Product Net Height:</b>	112 mm
<b>Product Net Length:</b>	81 mm
<b>Product Net Depth:</b>	112 mm
<b>Product Net Weight:</b>	0.21 kg

## Container Information

<b>Package Level 1 Width:</b>	159 mm
<b>Package Level 1 Length:</b>	337 mm
<b>Package Level 1 Height:</b>	135 mm
<b>Package Level 1 Gross Weight:</b>	0.3 kg
<b>Package Level 1 EAN:</b>	7392696793018
<b>Package Level 1 Units:</b>	10 piece

## Environmental

<b>RoHS Status:</b>	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q4
---------------------	---

## Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	2CMC700005D0001
<b>Environmental Information:</b>	2CMC700001D0002
<b>RoHS Information:</b>	2CMC700024

## Additional Information

<b>Additional Information:</b>	Cable entry,M25 knock-out
<b>Color:</b>	Purple
<b>Degree of Protection:</b>	acc. to IEC 60529 IP44
<b>Enclosure Material:</b>	Thermoplastic
<b>Frequency (f):</b>	50 Hz 60 Hz
<b>Function:</b>	Extra low voltage surface socket outlet

<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Invoice Description:</b>	Ind. P&S#CUGT 316
<b>Number of Poles:</b>	4
<b>Object Classification Code:</b>	2CMT005069
<b>Product Main Type:</b>	CUGT
<b>Product Name:</b>	Industrial Socket Outlet for Surface Mounting
<b>Protection Type:</b>	Splashproof
<b>Rated Current (I<sub>n</sub>):</b>	16 A
<b>Rated Voltage (U<sub>r</sub>):</b>	20 ... 25 V
<b>RoHS Date:</b>	2009-01
<b>Standards:</b>	IEC 60 309-1, -2
<b>Suitable For:</b>	Surface Socket Outlets
<b>Suitable for Product Class:</b>	Industrial Plugs and Sockets

---

## Classifications

---

<b>E-nummer:</b>	2416081
<b>UNSPSC:</b>	39120000

---

