

## 232-P6

ABB contact for United  
Kingdom**General Information**

<b>Extended Product Type:</b>	232-P6
<b>Product ID:</b>	2CMA193513R1000
<b>EAN:</b>	7392696935135
<b>Catalog Description:</b>	Plug, 6h, 32A, IP44, 2P+E
<b>Long Description:</b>	Plug, earthing sleeve position 6h, rated current 32A, IP44 splashproof, 2-poles+earth, 50 - 60 Hertz, color code blue

**Categories**

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs &amp; Sockets » Plugs

**Ordering**

<b>EAN:</b>	7392696935135
<b>Minimum Order Quantity:</b>	10 piece
<b>Country of Origin:</b>	Czech Republic (CZ)

**Dimensions**

<b>Product Net Width:</b>	90 mm
<b>Product Net Height:</b>	90 mm
<b>Product Net Length:</b>	162 mm
<b>Product Net Depth:</b>	90 mm
<b>Product Net Weight:</b>	0.196 kg

**Container Information**

<b>Package Level 1 Width:</b>	180 mm
<b>Package Level 1 Length:</b>	155 mm
<b>Package Level 1 Height:</b>	378 mm
<b>Package Level 1 Gross Weight:</b>	0.196 kg
<b>Package Level 1 EAN:</b>	7392696935135
<b>Package Level 1 Units:</b>	10 piece

**Environmental**

<b>RoHS Status:</b>	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
---------------------	------------------------------------------------------------------------------------------

**Certificates and Declarations (Document Number)**

<b>Declaration of Conformity - CE:</b>	2CMC700005D0001
<b>Environmental Information:</b>	2CMC700001D0002
<b>RoHS Information:</b>	2CMC700022

**Additional Information**

<b>Additional Information:</b>	Cable entry, compression gland
<b>Cable Cross-Section:</b>	2.5 ... 6 mm <sup>2</sup>
<b>Color:</b>	Blue
<b>Degree of Protection:</b>	IP44
<b>Enclosure Material:</b>	Polyamide
<b>Frequency (f):</b>	50 Hz 60 Hz
<b>Function:</b>	Plug
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Invoice Description:</b>	Ind. P&S#232-P6
<b>Number of Poles:</b>	3
<b>Object Classification Code:</b>	2CMT005069

ABB's website uses cookies. By staying here you are agreeing to our use of cookies. [Learn more](#) I agree

<b>Product Main Type:</b>	P
<b>Product Name:</b>	Industrial Plug
<b>Protection Type:</b>	Splashproof
<b>Rated Current (I<sub>n</sub>):</b>	32 A
<b>Rated Voltage (U<sub>r</sub>):</b>	200 ... 250 V
<b>RoHS Date:</b>	2009-1
<b>Standards:</b>	IEC 60309-1,-2
<b>Suitable For:</b>	Plugs
<b>Suitable for Product Class:</b>	Industrial Plugs and Sockets

## Classifications

<b>E-nummer:</b>	2416172
<b>UNSPSC:</b>	39120000

