




JUNCTION BOX

# Mini 25-L



## Mini 25-L

**Junction box**

89 x 43 x 37 mm

Article number: 31090801

Junction box acc. DIN EN 60670 (VDE 0606), 10 entries, 2 floor entries, suitable for confined installation environments such as suspended ceilings and cable ducts, complete with perforation tool and blanking plug, with external fixing positions

grey, without terminals, for VDE approved single terminals



## Technical data

### Measures

Width:	89 mm
Length:	43 mm
Height:	37 mm

### Material

Base:	Polyethylene
Cover:	Polypropylene

### Other attributes

Color:	grey
Rated cross section:	2,5 mm²
Tackable:	No
Rated insulation voltage AC:	400 V
Explosion safety:	none
Fire protection:	none

## Accessory

- VST RR - Blanking plugs
- HandyClip VC 20 - Single terminal
- HandyGrip VG 20 - Terminal strip
- HandyGrip VG 20 w - Terminal strip
- HandyGrip VG 21 - Terminal strip
- HandyGrip VG 21 w - Terminal strip
- HandyQuick SQ 32 - screwless terminal
- HandyQuick SQ 52 - screwless terminal



JUNCTION BOX

# Mini 25-L

sealable:	No
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP55 - acc. EN 60529 / DIN VDE 0470-1
Weatherproof:	No
Equipment:	None

## Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short Therm):	95%
Max. rel. humidity at 40° C:	50%