



JUNCTION BOX

# Sd 7-L



## Sd 7-L

**Junction box**

75 x 75 x 37 mm

Article number: 33290701

Junction box acc. DIN EN 60670 (VDE 0606), 7 entries, 3 floor entries, complete with perforation tool and blanking plug, with external fixing positions

grey, without terminals, for VDE approved single terminals



## Technical data

### Measures

Width:	75 mm
Length:	75 mm
Height:	37 mm

### Material

Base:	Polyethylene
Cover:	Polypropylene

### Other attributes

Rated cross section:	2,5 mm²
Tackable:	No
Rated insulation voltage AC:	400 V
Explosion safety:	none
Fire protection:	none
sealable:	No

## Accessory

VST RR - Blanking plugs

HandyGrip VG 20 - Terminal strip

HandyGrip VG 20 w - Terminal strip

HandyGrip VG 21 - Terminal strip

HandyGrip VG 21 w - Terminal strip

HandyQuick SQ 32 - screwless terminal

HandyQuick SQ 52 - screwless terminal



JUNCTION BOX

# Sd 7-L

Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP55 - acc. EN 60529 / DIN VDE 0470-1
Weatherproof:	No
Equipment:	None
Color:	grey

## Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short Therm):	95%
Max. rel. humidity at 40° C:	50%