



JUNCTION BOX

i 12-L



i 12-L

Junction box

85 x 85 x 37 mm

Article number: 33291201

Junction box acc. DIN EN 60670 (VDE 0606), 12 entries, 3 floor entries, complete with perforation tool and blanking plug, with external fixing positions

grey, without terminals, for VDE approved single terminals



Technical data

Measures

Width:	85 mm
Length:	85 mm
Height:	37 mm

Material

Base:	Polyethylene
Cover:	Polypropylene

Other attributes

Color:	miscellaneous
Rated cross section:	2,5 mm²
Tackable:	No
Rated insulation voltage AC:	400 V
Explosion safety:	none
Fire protection:	none

Accessory

- VST RR - Blanking plugs
- HandyGrip VG 20 - Terminal strip
- HandyGrip VG 20 w - Terminal strip
- HandyGrip VG 21 - Terminal strip
- HandyGrip VG 21 w - Terminal strip
- HandyQuick SQ 32 - screwless terminal
- HandyQuick SQ 52 - screwless terminal



JUNCTION BOX

i 12-L

sealable:	No
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP55 - acc. EN 60529 / DIN VDE 0470-1
Weatherproof:	No

Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short Therm):	95%
Max. rel. humidity at 40° C:	50%