



JUNCTION BOX

Q 4-L



Q 4-L

Junction box

56 x 40 x 23 mm

Article number: 33490401

Junction box acc. DIN EN 60598 (VDE 0711), 4 entries, with strain relief acc. VDE 0606, 2 of which are accessible from the top, strain relief clamp for pendulum lights, with external fixing positions

grey, without terminal



Technical data

Measures

Width:	56 mm
Length:	40 mm
Height:	23 mm

Material

Base:	Polypropylene
Cover:	Polypropylene

Other attributes

Color:	grey
Rated cross section:	2,5 mm <sup>2</sup>
Tackable:	No
Entries:	4
sealable:	No
Rated insulation voltage AC:	400 V



JUNCTION BOX

**Q 4-L**

Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP20 - acc. EN 60529 / DIN VDE 0470-1
Weatherproof:	No
Equipment:	None

**Environmental attributes**

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short Therm):	95%
Max. rel. humidity at 40° C:	50%