



JUNCTION BOX

Mini 25-2,5²



Mini 25-2,5²

Junction box

89 x 43 x 37 mm

Article number: 31040801

Junction box acc. DIN EN 60670 (VDE 0606), 10 entries, 2 floor entries, suitable for confined installation environments such as suspended ceilings and cable ducts, complete with perforation tool and blanking plug, with external fixing positions

grey, with 3 interlockable screw terminals 2.5 mm²



Technical data

Measures

Width:	89 mm
Length:	43 mm
Height:	37 mm

Material

Base:	Polyethylene
Cover:	Polypropylene

Other attributes

Color:	grey
Rated cross section:	2,5 mm ²
Tackable:	No
Rated insulation voltage AC:	400 V
Explosion safety:	none
Fire protection:	none

Accessory

- VST RR - Blanking plugs
- HandyClip VC 20 - Single terminal
- HandyGrip VG 20 - Terminal strip
- HandyGrip VG 20 w - Terminal strip
- HandyGrip VG 21 - Terminal strip
- HandyGrip VG 21 w - Terminal strip
- HandyQuick SQ 32 - screwless terminal
- HandyQuick SQ 52 - screwless terminal



JUNCTION BOX

Mini 25-2,5²

sealable: No

Heavy metals-free: Yes

PVC-free: Yes

Silicone-free: Yes

Ingress protection: IP55 - acc. EN
60529 / DIN VDE
0470-1

Weatherproof: No

Equipment: Terminal

Environmental attributes

Ambient temperature (min.): -25 °C

Ambient temperature (max.): 40 °C

Ambient temperature (24 h): 35 °C

Max. rel. humidity at 25° C (short
Therm): 95%

Max. rel. humidity at 40° C: 50%